


イグリデュールJ — フランジ型ベアリング — タイプF



- f = 0.3 ▶ d1 = 1~6
- f = 0.5 ▶ d1 = 6~12
- f = 0.8 ▶ d1 = 12~30
- f = 1.2 ▶ d1 > 30

内径d1を面取り加工
ISO 3547-1による寸法公差

製品番号の構成

J F M-03 04 - 05



製品番号	d1*	d2	d3		b2
			d13	h13	
JFM-0304-05	3.0	4.5	7.5	5.0	0.75
JFM-0306-10	3.0	6.0	9.0	10.0	1.5
JFM-0405-03	4.0	5.5	9.5	3.0	0.75
JFM-0405-06	4.0	5.5	9.5	6.0	0.75
JFM-0507-05	5.0	7.0	11.0	5.0	1.0
JFM-0608-04	6.0	8.0	12.0	4.0	1.0
JFM-0608-06	6.0	8.0	12.0	6.0	1.0
JFM-0608-08	6.0	8.0	12.0	8.0	1.0
JFM-0608-10	6.0	8.0	12.0	10.0	1.0
JFM-0610-10	6.0	10.0	14.0	10.0	2.0
JFM-0810-038	8.0	10.0	15.0	3.8	1.0
JFM-0810-05	8.0	10.0	15.0	5.0	1.0
JFM-0810-06	8.0	10.0	15.0	6.0	1.0
JFM-0810-07	8.0	10.0	15.0	7.0	1.0
JFM-0810-08	8.0	10.0	15.0	8.0	1.0
JFM-0810-10	8.0	10.0	15.0	10.0	1.0
JFM-0810125-10	8.0	10.0	12.5	10.0	1.0
JFM-081014-10	8.0	10.0	14.0	10.0	1.0
JFM-081016-11	8.0	10.0	16.0	11.0	2.0
JFM-0812-06	8.0	12.0	16.0	6.0	2.0
JFM-1012-05	10.0	12.0	18.0	5.0	1.0
JFM-1012-09	10.0	12.0	18.0	9.0	1.0
JFM-1012-10	10.0	12.0	18.0	10.0	1.0
JFM-1012-12	10.0	12.0	18.0	12.0	1.0
JFM-1012-15	10.0	12.0	18.0	15.0	1.0
JFM-1012-18	10.0	12.0	18.0	18.0	1.0
JFM-101215-035	10.0	12.0	15.0	3.5	1.0
JFM-1113-05	11.0	13.0	18.0	5.0	1.0
JFM-1214-05	12.0	14.0	20.0	5.0	1.0
JFM-1214-07	12.0	14.0	20.0	7.0	1.0
JFM-1214-09	12.0	14.0	20.0	9.0	1.0
JFM-1214-12	12.0	14.0	20.0	12.0	1.0
JFM-1214-15	12.0	14.0	20.0	15.0	1.0
JFM-121418-045	12.0	14.0	18.0	4.5	1.0
JFM-121418-10	12.0	14.0	18.0	10.0	1.0
JFM-1218-08	12.0	18.0	24.0	8.0	3.0
JFM-1218-12	12.0	18.0	24.0	12.0	3.0
JFM-1218-20	12.0	18.0	22.0	20.0	3.0
JFM-1416-03	14.0	16.0	22.0	3.0	1.0
JFM-1416-10	14.0	16.0	22.0	10.0	1.0
JFM-1416-12	14.0	16.0	22.0	12.0	1.0
JFM-1416-17	14.0	16.0	22.0	17.0	1.0
JFM-141822-20	14.0	18.0	22.0	20.0	2.0
JFM-1517-09	15.0	17.0	23.0	9.0	1.0

製品番号	d1*	d2	d3		b2
			d13	h13	
JFM-1517-12	15.0	17.0	23.0	12.0	1.0
JFM-1517-17	15.0	17.0	23.0	17.0	1.0
JFM-1521-20	15.0	21.0	27.0	20.0	3.0
JFM-1618-17	16.0	18.0	24.0	17.0	1.0
JFM-1622-12	16.0	22.0	28.0	12.0	3.0
JFM-1622-15	16.0	22.0	28.0	15.0	3.0
JFM-1719-09	17.0	19.0	25.0	9.0	1.0
JFM-1719-21	17.0	19.0	25.0	21.0	1.0
JFM-1820-04	18.0	20.0	26.0	4.0	1.0
JFM-1820-12	18.0	20.0	26.0	12.0	1.0
JFM-1820-22	18.0	20.0	26.0	22.0	1.0
JFM-1922-36	19.0	22.0	26.0	36.0	1.0
JFM-2023-11	20.0	23.0	30.0	11.5	1.5
JFM-2023-15.5	20.0	23.0	30.0	15.5	1.5
JFM-2023-21	20.0	23.0	30.0	21.5	1.5
JFM-202530-15	20.0	25.0	30.0	15.0	2.0
JFM-2026-20	20.0	26.0	32.0	20.0	3.0
JFM-2026-25	20.0	26.0	32.0	25.0	3.0
JFM-222532-08	22.0	25.0	32.0	8.0	1.5
JFM-2430-30	24.0	30.0	36.0	30.0	3.0
JFM-2528-06	25.0	28.0	35.0	6.0	1.5
JFM-2528-14.5	25.0	28.0	35.0	14.5	1.5
JFM-2528-21	25.0	28.0	35.0	21.5	1.5
JFM-252839-075	25.0	28.0	39.0	7.5	1.5
JFM-2532-20	25.0	32.0	38.0	20.0	4.0
JFM-2532-25	25.0	32.0	38.0	25.0	4.0
JFM-283235-07	28.0	32.0	35.0	7.0	2.0
JFM-3034-20	30.0	34.0	42.0	20.0	2.0
JFM-3034-26	30.0	34.0	42.0	26.0	2.0
JFM-3038-30	30.0	38.0	44.0	30.0	4.0
JFM-3539-12	35.0	39.0	47.0	12.0	2.0
JFM-3539-16	35.0	39.0	47.0	16.0	2.0
JFM-3539-26	35.0	39.0	47.0	26.0	2.0
JFM-4044-20	40.0	44.0	52.0	20.0	2.0
JFM-4044-30	40.0	44.0	52.0	30.0	2.0
JFM-4044-40	40.0	44.0	52.0	40.0	2.0
JFM-4550-20	45.0	50.0	58.0	20.0	2.0
JFM-4550-50	45.0	50.0	58.0	50.0	2.0
JFM-5055-50	50.0	55.0	63.0	50.0	2.0
JFM-5560-50	55.0	60.0	68.0	50.0	2.0
JFM-6065-50	60.0	65.0	73.0	50.0	2.5
JFM-7075-50	70.0	75.0	83.0	50.0	2.0

* イグリデュールJの公差等級：E10

イグリデュールJ

電話：03-5819-2030
FAX：03-5819-2055

