


SFC・SRC

ねじ込み形管継手


SFC カップリング



単位：mm

継手の呼び	T (Rc)	H (六角)	L	重量 (kg)
SFC01-000J	1/8	19	30	0.059
SFC02-000F	1/4	22	30	0.075
SFC03-000F	3/8	24	30	0.074
SFC04-000F	1/2	32	40	0.19
SFC06-000F	3/4	36	42	0.21
SFC08-000F	1	46	50	0.43
SFC10-000F	1 1/4	55	55	0.61
SFC12-000F	1 1/2	65	55	0.89
SFC16-000F	2	75	64	1.17

SRC レジューサ



単位：mm

継手の呼び	T×T1 (Rc)	H (六角)	L	重量 (kg)
SRC03-020F	3/8 × 1/4	24	30	0.083
SRC04-020F	1/2 × 1/4	32	40	0.22
SRC04-030F	1/2 × 3/8	32	40	0.21
SRC06-020F	3/4 × 1/4	36	42	0.28
SRC06-030F	3/4 × 3/8	36	42	0.27
SRC06-040F	3/4 × 1/2	36	42	0.25
SRC08-030F	1 × 3/8	46	50	0.55
SRC08-040F	1 × 1/2	46	50	0.53
SRC08-060F	1 × 3/4	46	50	0.50
SRC10-040F	1 1/4 × 1/2	55	55	0.81
SRC10-060F	1 1/4 × 3/4	55	55	0.77
SRC10-080F	1 1/4 × 1	55	55	0.71
SRC12-060F	1 1/2 × 3/4	65	55	1.14
SRC12-080F	1 1/2 × 1	65	55	1.08
SRC12-100F	1 1/2 × 1 1/4	65	55	0.97
SRC16-080F	2 × 1	75	64	1.64
SRC16-100F	2 × 1 1/4	75	64	1.51
SRC16-120F	2 × 1 1/2	75	64	1.41