



BI-LoK	MDTA	Union Tee Connects metric tubes
---------------	-------------	---



Part No.	A	E	h	H	ℓ	L	F
	mm	mm	Flat	HEX	mm	mm	mm
MDTA 2M	2	1.3	12	12	16.8	22.4	11.2
MDTA 3M	3	2.4	12	12	16.8	23.5	13.0
MDTA 4M	4	2.7	12	13	19.0	25.8	13.9
MDTA 6M	6	4.8	12	14	22.2	29.7	15.4
MDTA 6M E	6	4.8	12	14	19.6	27.1	15.4
MDTA 8M	8	6.4	14	17	22.5	30.0	16.3
MDTA 10M	10	7.9	17	19	24.0	31.8	17.3
MDTA 12M	12	9.5	22	22	27.0	37.2	22.9
MDTA 15M	15	12.0	24	27	28.0	38.0	24.3
MDTA 16M	16	12.7	24	27	28.0	38.2	24.5
MDTA 18M	18	15.1	27	30	28.2	38.4	24.5
MDTA 20M	20	16.5	30	30	32.5	42.7	24.5
MDTA 22M	22	18.3	30	32	32.5	42.7	26.1
MDTA 25M	25	22.5	36	41	36.0	48.5	31.6

[Note] E :European Standard

BI-LoK	MDTR	Reducing Union Tee Connects metric tubes
---------------	-------------	--



Part No.	A	A ₁	E	E ₁	h	H	H ₁	ℓ	L	L ₁	F	F ₁
	mm	mm	mm	mm	Flat	HEX	HEX	mm	mm	mm	mm	mm
MDTR 8M-6M	8	6	6.4	4.8	14	17	14	22.5	30.0	30.0	16.3	15.4
MDTR 10M-6M	10	6	7.9	4.8	17	19	14	24.0	31.8	31.5	17.3	15.4
MDTR 10M-8M	10	8	7.9	6.4	17	19	17	24.0	31.8	31.5	17.3	16.3
MDTR 12M-16M	12	16	9.5	12.7	24	22	27	28.0	38.2	38.2	22.9	24.5
MDTR 12M-25M	12	25	9.5	22.5	36	22	41	36.0	46.2	48.5	22.9	31.6
MDTR 16M-8M	16	8	12.7	6.4	24	27	17	28.0	38.2	35.5	24.5	16.3
MDTR 16M-10M	16	10	12.7	7.9	24	27	19	28.0	38.2	35.8	24.5	17.3
MDTR 16M-12M	16	12	12.7	9.5	24	27	22	28.0	38.2	38.2	24.5	22.9
MDTR 16M-22M	16	22	12.7	18.3	30	27	32	32.5	42.7	42.7	24.5	26.1
MDTR 18M-10M	18	10	15.1	7.9	27	30	19	28.2	38.4	36.0	24.5	17.3
MDTR 18M-12M	18	12	15.1	9.5	27	30	22	28.2	38.4	38.4	24.5	22.9
MDTR 20M-12M	20	12	16.5	9.5	30	30	22	32.5	42.7	42.7	24.5	22.9
MDTR 20M-16M	20	16	16.5	12.7	30	30	27	32.5	42.7	42.7	24.5	24.5
MDTR 22M-8M	22	8	18.3	6.4	30	32	17	32.5	42.7	40.0	26.1	16.3
MDTR 22M-18M	22	18	18.3	15.1	30	32	30	32.5	42.7	42.7	26.1	24.5
MDTR 25M-10M	25	10	22.5	7.9	36	41	19	36.0	48.5	43.8	31.6	17.3
MDTR 25M-12M	25	12	22.5	9.5	36	41	22	36.0	48.5	46.2	31.6	22.9
MDTR 25M-16M	25	16	22.5	12.7	36	41	27	36.0	48.5	46.2	31.6	24.5
MDTR 25M-20M	25	20	22.5	16.5	36	41	30	36.0	48.5	46.2	31.6	24.5