



LM

LM-AJ

LM-OP

F_w	主要寸法及び許容差 mm													偏心		基本動定格荷重		基本静定格荷重		
	寸法差 μm		D	寸法差 μm		C	寸法差 μm		C_2	D_1	h	E	α 度	最大 μm	精	上	C		C_0	
	精	上		精	上		精	上									荷重方向A N	荷重方向B N	荷重方向A N	荷重方向B N
6			12		19		13.5		1.1	11.5	- 1	-	-				80.7	92.7	167	237
8			15	0 -11	17		11.5		1.1	14.3	- 1	-	-				87.4	100	160	226
8			15		24		17.5		1.1	14.3	- 1	-	-				121	139	255	361
10	0 -6	0 -9	19		29	0	22	0	1.3	18	- 1	-	-	8	12		179	206	354	501
12			21	0	30	-200	23	-200	1.3	20	1.5	8	80				259	298	503	711
13			23	-13	32		23		1.3	22	1.5	9	80				266	306	506	716
16			28		37		26.5		1.6	27	1.5	11	80				426	489	766	1 080
20			32		42		30.5		1.6	30.5	1.5	11	60				562	668	1 010	1 470
25	0 -7	0 -10	40	0 -16	59		41		1.85	38	2	12	50	10	15		920	974	1 780	2 280
30			45		64		44.5		1.85	43	2.5	15	50				1 350	1 430	2 500	3 200
35			52		70	0 -300	49.5	0 -300	2.1	49	2.5	17	50				1 610	1 710	3 080	3 940
40	0 -8	0 -12	60	0 -19	80		60.5		2.1	57	3	20	50	12	20		2 030	2 150	3 620	4 640
50			80		100		74		2.6	76.5	3	25	50				3 940	4 180	7 130	9 120

1N=0.102kgf