

AMNS-S


COMPACT PNEUMATIC WORK SUPPORTS



★Key Point

Provide high support capacity even with small body.

Body	Piston / Locking Shaft	Cylinder
A5052 aluminum Anodized	S45C steel Electroless nickel plated	A5056 aluminum Anodized



Part Number	H	H ₁	M ₁	H ₂	D	L	W	d	M	L ₁
AMNS06-S	25	33	M4×0.7	7	4	36	8	3.4	M3×0.5 6-deep	7
AMNS08-S	32	44	M6×1	10.5	6	46	10	4.5	M4×0.7 8-deep	9

Part Number	L ₂	P	H ₃	H ₄	Operating Air Pressure (MPa)	Support Capacity (N)	Piston Spring Force (N) (Note)	Weight (g)
AMNS06-S	6	10	10	3	0.3~0.7	15~40	0.2~0.3	22
AMNS08-S	7.5	13	13	5		30~70	0.3~0.4	49

Note: Support Capacity is the force of the inner spring to lift the piston up.