


AMWPD-X

CLAMPING PINS



Note: L dimension is adjustable by ± 1 mm to fit actual workpiece thickness.


Shank	Head
Steel (SCM435) Induction hardened (taper seat) Precision ground	Steel (S45C) Quenched and tempered Black oxide finish

Part Number	D ₂ (f7)	D ₁ (f7)	L [*] (By 0.1mm)	D	L ₂	L ₁	L ₃	D ₃	M
AMWPD40- 8- (L Dim. in mm)	8	8	4 ≤ L ≤ 64	16	15	38	24	4.3	M5×0.8 -5L
AMWPD40-10- (L Dim. in mm)		10							
AMWPD63-12- (L Dim. in mm)	12	12	0 < L ≤ 90	18	23	48	31.5	6.5	M8×1.25-8L
AMWPD63-16- (L Dim. in mm)		16		24					

Part Number	M ₁	Proper Pull Clamps	Weight (g)
AMWPD40- 8- (L Dim. in mm)	M5×0.8	AMWPD40-W	min. 30~max. 60
AMWPD40-10- (L Dim. in mm)			min. 31~max. 77
AMWPD63-12- (L Dim. in mm)	M8×1.25	AMWPD63-W	min. 70~max.160
AMWPD63-16- (L Dim. in mm)			min.175~max.265

*) For ordering, specify workpiece thickness.

How To Use



Note

The length of L dimension should be decided depending on the workpiece thickness.

Ordering Example

AMWPD40-8 - 10.5

Shank Size

L Dim.