



Body
Ductile cast iron(FCD450)
Powder baked finish
Black

Part Number	A	B	C	D	E	F	G	Weight (g)
BK50×12T	50	54	29	22	13	13	M12×1.75	335
BK50×16T							M16×2	315
BK63×12T	63	59	38	22.5	14.5	17	M12×1.75	600
BK63×16T							M16×2	575
BK90×20T	90	54				32	M20×2.5	1,305
BK90×24T							M24×3	1,270

- Insert a bar between the prongs for maximum leverage and holding force.