




BSFJ BALL SCREWS, Plastic Ball



Body	Ball
Steel (SUM22L) Black oxide finish	Polyacetal plastic

Part Number	Ball Dia.	A	B	C	D	E	Weight (g)
BSFJ4× 6	Sφ2.5	5.9	M4×0.7	1.8	2	0.2	0.3
BSFJ4× 8		7.9					0.4
BSFJ4×10		9.9					0.5
BSFJ4×12		11.9					0.6
BSFJ4×16		15.9					0.9
BSFJ5× 8	Sφ3	7.8	M5×0.8	2.1	2.5	0.3	0.6
BSFJ5×10		9.8					0.8
BSFJ5×12		11.8					1
BSFJ5×16		15.8					1.5
BSFJ5×20		19.8					1.9
BSFJ5×25	24.8	2.5					
BSFJ6×10	Sφ4	10.3	M6×1	3	3	0.4	1.3
BSFJ6×12		12.3					1.5
BSFJ6×16		16.3					2
BSFJ6×20		20.3					2.7
BSFJ6×25		25.3					3.4
BSFJ8×10	Sφ5.5	10.4	M8×1.25	4.2	4	0.5	1.8
BSFJ8×12		12.4					2.3
BSFJ8×16		16.4					3.1
BSFJ8×20		20.4					4.6
BSFJ8×25		25.4					6
BSFJ8×30		30.4					7.6

• Heat resistance : 95°C