


**BJ748****CLAMP SCREWS**

Body
Steel(SCM435)
Black oxide finish
Quenched and tempered (Rc 33 - 39)

Part Number	M	L	W	D	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	R	Clamping Force (kN)	Allowable Screw Torque (N·m)	Weight (g)
<b>BJ748-06030</b>	M 6×1	30	10	4.5	8	27	2.5	R 5	8	10	9
<b>BJ748-06040</b>		40				37					10
<b>BJ748-06050</b>		50				47					12
<b>BJ748-08040</b>	M 8×1.25	40	13	5.5	10	37	3	R 6	16	25	21
<b>BJ748-08050</b>		50				47					24
<b>BJ748-08060</b>		60				57					26
<b>BJ748-10040</b>	M10×1.5	40	17	7.5	12	37	3.5	R 8	25	50	38
<b>BJ748-10050</b>		50				47					42
<b>BJ748-10060</b>		60				57					46
<b>BJ748-12060</b>	M12×1.75	60	19	9	15	55	5	R 9	38	90	70
<b>BJ748-12080</b>		80				75					80
<b>BJ748-12100</b>		100				95					95
<b>BJ748-12125</b>	M16×2	125	24	12	20	120	6	R12	63	200	115
<b>BJ748-16080</b>		80				75					165
<b>BJ748-16100</b>		100				95					185
<b>BJ748-16125</b>	M20×2.5	125	30	15	25	120	7	R15	98	390	215
<b>BJ748-16150</b>		150				145					270
<b>BJ748-20080</b>		80				70					285
<b>BJ748-20100</b>	M20×2.5	100	30	15	25	90	7	R15	98	390	320
<b>BJ748-20125</b>		125				115					365
<b>BJ748-24100</b>		100				90					460
<b>BJ748-24125</b>	M24×3	125	36	19.5	25	115	8	R20	140	670	525
<b>BJ748-24150</b>		150				140					590

**How To Use**