

EFTH

PLASTIC HINGES



Original ELESA Model CFM.




EFTH-TT
(Stud)



EFTH-HH
(Through)



EFTH-HH-CL
(Through)



Body	Pivot Pin	Stud
Polyamide (glass-fiber reinforced)	Stainless steel (SUS303)	Steel(SUM22L)
Black matte		Nickel plated
Gray white		


EFTH-HH **EFTH-HH-CL** (Through)

Black matte	Gray white	W	L	P	H	T	d	d ₁	E	A	D	Weight (g)
Part Number	Part Number											
EFTH4040HH	EFTH4040HH-CL	40	40	25	9	5	10.5	5.5	5.5	14	4	14
EFTH5050HH	EFTH5050HH-CL	50	50	30	11.5	6	12.5	6.5	6.5	18	6	30
EFTH6060HH	EFTH6060HH-CL	60	60	36	15	8	16.5	8.5	8.5	21	8	57

EFTH-TT (Stud)

Part Number	W	L	P	H	T	M	L ₁	E	A	D	Weight (g)
EFTH4040TT	40	40	25	9	5	M5×0.8	12	5.5	14	4	26
EFTH5050TT	50	50	30	11.5	6	M6×1	12	6.5	18	6	50
EFTH6060TT	60	60	36	15	8	M8×1.25	14.5	8.5	21	8	101

How To Use



Technical Information

- Pivot angle : Up to 270°
- Working temperature : -30 to 140°C

Caution

Use in hot or highly humid circumstances can deteriorate the plastic properties.