

EFHP PLASTIC HINGES




EFHP7050HH
(Through)




EFHP7050TT
(Stud)


Body	Pivot Pin	Insert	Stud
Polyamide plastic Black matte	Stainless steel (SUS303)	Brass Nickel plated finish	Steel (SUM22L) Nickel plated finish






EFHP7050SS
(Tapped)



EFHP7050TT
(Stud)



EFHP7050HH
(Through)



Part Number	Weight (g)
EFHP7050SS	66
EFHP7050TT	71
EFHP7050HH	46

- Pin-embedded design suitable for hygienic applications.
- Pivot angle : Max. 270°
- Working temperature : Between -20°C and 80°C
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.