


ESJA PLASTIC HINGES




ELESA Original Design CFO.




| Body / Cover Cap | Pivot Pin | End Cap |
|---|-----------------------------|---|
| Glass-fiber reinforced polyamide plastic Black matte | Polyacetal plastic Black | Polyamide plastic Glossy Finish Black |

| Part Number | Load Capacity (N) | | Max. Screw Torque (N·m) | Weight (g) |
|-----------------|-------------------|------------|-------------------------|------------|
| | Radial Load | Axial Load | | |
| ESJA3564 | 200 | 290 | 5 | 25 |



- Can mount on doors that open on the right or left side.
- Allows adjusting the angle between the wall and the door.
- For face mounting, use M5 hex. socket-head cap screws or M5 hex. screws. For back mounting, use M5 hex. socket-head cap screws and hex. nuts.
- Working temperature : Between -20°C and 80°C

How To Assemble



- Use in hot or highly humid circumstances can deteriorate the plastic material properties.