



EMH PLASTIC HINGES




ELESA Original Design CFF.



EMH-SS
(Tapped)



EMH-SS
(Tapped)



EMH-TT
(Stud)

Body	Pivot Pin	Insert	Stud
Polyamide plastic Black matte	Stainless steel (SUS303)	Brass Nickel plated finish	Steel (SUM22L) Nickel plated finish


EMH-SS (Tapped)

Part Number	A	B	C	D	E	F	G	H	J	Weight (g)
EMH2030SS	19	30.5	7	15	12.5	9.5	2.5	M3X0.5	4	6
EMH2540SS	24	40.5	9.5	20	16.5	12	4	M4X0.7	5.5	14
EMH3050SS	30	48.5	11.5	24	20	15	5	M5X0.8	6.5	23
EMH4065SS	42	66	15	33	27.5	21	6	M6X1	9	54

EMH-TT (Stud)

Part Number	A	B	C	D	E	F	G	K	L	Weight (g)
EMH2030TT	19	30.5	7	15	12.5	9.5	2.5	M3X0.5	13	8
EMH2540TT	24	40.5	9.5	20	16.5	12	4	M4X0.7	18	20
EMH3050TT	30	48.5	11.5	24	20	15	5	M5X0.8	17	33
EMH4065TT	42	66	15	33	27.5	21	6	M6X1	16	64

How To Use



- Pivot angle : Max. 200°
- Working temperature : Between -20°C and 80°C
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.