

RGS (Phenolic)

Part Number	D	M	D ₁	H	L	W	Weight (g)
RGS 40	18	M 6×1	15	40	13	4	28
RGS 50	21	M 8×1.25	17	50	15	5	52
RGS 65	23		19	65	17	6	86
RGS 80	26	M10×1.5	21	80	18		8
RGS 90	28		22	90		170	
RGS100	31	M12×1.75	25	102	20		245

RG-N **RG-N-SUS** (Polypropylene)

Steel Shank Part Number	Stainless-Steel Shank Part Number	D	M	D ₁	H	L	W	Weight (g)
RG40N	RG40N-SUS	18	M 6×1	15	40	13	3	25
RG50N	RG50N-SUS	21		17	50			35
RG65N	RG65N-SUS	23	M 8×1.25	19	65	15	4	68
RG80NB	-	26		21	80			75
RG80N	RG80N-SUS	28	M10×1.5	22	90	17	5	78
RG90N	RG90N-SUS							85

Features

- The **RG** **RG-N** and **RG-N-SUS** types are provided with a hex. wrench hole at the end of the shank for installation.
- The **RGS** type is provided with a hex. wrench hole on the top of the handle for installation.

Technical Information

Working temperature: **RG** **RGS** max. 110°C min. -20°C
RG-N **RG-N-SUS** max. 80°C min. 0°C