


寸法表

3V1本掛

(mm)


呼び径 de	ピッチ径 d m	軸 穴		形 状 図 番	ボ ス				総 幅 L	リ ム		質 量 (kg)	不釣り合い 質量許容値 (g)	GD ² (kg·m ²)
		最大径	下穴径d		径 db	長さ l	出S ₁	引込S ₂		厚さH	幅 B			
67	65.8	25	10	①の1	45	25	7.6	—	25	—	17.4	0.49	0.5	0.0009
70	68.8	25	10	①の1	45	25	7.6	—	25	—	17.4	0.53	0.6	0.0010
71	69.8	25	10	①の1	45	25	7.6	—	25	—	17.4	0.54	0.6	0.0011
75	73.8	28	10	①の1	50	28	10.6	—	28	—	17.4	0.65	0.7	0.0014
80	78.8	28	10	①の1	50	28	10.6	—	28	—	17.4	0.73	0.8	0.0018
85	83.8	28	10	①の1	50	28	10.6	—	28	—	17.4	0.85	0.9	0.0022
90	88.8	32	13	①の1	60	32	14.6	—	32	—	17.4	1.05	1.1	0.0031
95	93.8	32	13	①の1	60	32	14.6	—	32	—	17.4	1.2	1.2	0.0038
100	98.8	32	13	①の1	60	32	14.6	—	32	—	17.4	1.25	1.3	0.0046
110	108.8	32	13	①の1	60	32	14.6	—	32	—	17.4	1.45	1.5	0.0065
112	110.8	32	13	①の1	60	32	14.6	—	32	—	17.4	1.5	1.5	0.0070
120	118.8	32	13	①の1	60	32	14.6	—	32	—	17.4	1.7	1.7	0.0092
125	123.8	35	15	①の1	65	35	17.6	—	35	—	17.4	1.8	1.8	0.0102
130	128.8	35	15	①の1	65	35	17.6	—	35	—	17.4	2.1	2.1	0.0129
140	138.8	35	15	①の1	65	35	17.6	—	35	—	17.4	2.3	2.3	0.0173
150	148.8	35	15	①の1	65	35	17.6	—	35	—	17.4	2.6	2.6	0.0226
160	158.8	35	15	①の2	65	35	17.6	—	35	17	17.4	2.3	2.3	0.0229
180	178.8	42	18	①の2	75	42	24.6	—	42	17	17.4	3.1	3.1	0.0368
200	198.8	42	18	①の2	75	42	24.6	—	42	17	17.4	3.3	3.3	0.0510
212	210.8	42	18	①の2	75	42	24.6	—	42	15	17.4	3.2	3.2	0.0583
224	222.8	42	18	①の2	75	42	24.6	—	42	15	17.4	3.3	3.3	0.0684
236	234.8	42	18	①の2	75	42	24.6	—	42	15	17.4	3.4	3.4	0.0798
250	248.8	42	20	①の2	75	42	24.6	—	42	17	17.4	3.9	3.9	0.109
280	278.8	42	20	①の2	75	42	24.6	—	42	17	17.4	4.5	4.5	0.160
300	298.8	42	22	①の2	75	42	24.6	—	42	17	17.4	4.8	4.8	0.203
315	313.8	50	22	①の2	90	48	30.6	—	48	17	17.4	6.2	6.2	0.253
360	358.8	50	22	①の2	90	50	32.6	—	50	17	17.4	8.5	8.5	0.36



3V2本掛

(mm)

呼び径 de	dm	軸 穴		形 状 図 番	ボ ス				総 幅 L	リ ム		質 量 (kg)	不釣り合い 質量許容値 (g)	GD ² (kg·m ²)
		最大径	下穴径d		径 db	長さ l	出S ₁	引込S ₂		厚さH	幅 B			
67	65.8	28	13	①の1	50	35	7.3	—	35	—	27.7	0.70	0.7	0.0012
70	68.8	28	13	①の1	50	35	7.3	—	35	—	27.7	0.76	0.8	0.0014
71	69.8	28	13	①の1	50	35	7.3	—	35	—	27.7	0.78	0.8	0.0015
75	73.8	32	13	①の1	60	35	7.3	—	35	—	27.7	0.95	1.0	0.0020
80	78.8	32	13	①の1	60	35	7.3	—	35	—	27.7	1.1	1.1	0.0026
85	83.8	32	13	①の1	60	35	7.3	—	35	—	27.7	1.2	1.2	0.0033
90	88.8	32	13	①の1	60	35	7.3	—	35	—	27.7	1.3	1.3	0.0041
95	93.8	32	13	①の1	60	35	7.3	—	35	—	27.7	1.4	1.4	0.0051
100	98.8	38	15	①の1	65	35	7.3	—	35	—	27.7	1.6	1.6	0.0064
110	108.8	38	15	①の1	65	35	7.3	—	35	—	27.7	1.9	1.9	0.0094
112	110.8	38	15	①の1	65	35	7.3	—	35	—	27.7	2.0	2.0	0.0102
120	118.8	38	15	①の1	65	35	7.3	—	35	—	27.7	2.3	2.3	0.0134
125	123.8	42	18	①の1	75	42	14.3	—	42	—	27.7	2.5	2.5	0.0152
130	128.8	42	18	①の1	75	42	14.3	—	42	—	27.7	3.0	3.0	0.0196
140	138.8	42	18	①の1	75	42	14.3	—	42	—	27.7	3.3	3.3	0.0263
150	148.8	42	18	①の1	75	42	14.3	—	42	—	27.7	3.8	3.8	0.0330
160	158.8	42	18	①の2	75	42	14.3	—	42	17	27.7	4.3	4.3	0.0345
180	178.8	50	20	①の2	90	48	20.3	—	48	17	27.7	4.6	4.6	0.0539
200	198.8	50	20	①の2	90	48	20.3	—	48	17	27.7	5.0	5.0	0.0721
212	210.8	50	20	①の2	90	48	20.3	—	48	15	27.7	4.7	4.7	0.0864
224	222.8	50	20	①の2	90	48	20.3	—	48	15	27.7	4.9	4.9	0.101
236	234.8	50	20	①の2	90	48	20.3	—	48	15	27.7	5.1	5.1	0.117
250	248.8	50	20	①の2	90	48	20.3	—	48	17	27.7	6.0	6.0	0.152
280	278.8	55	20	①の2	100	55	27.3	—	55	17	27.7	7.6	7.6	0.237
300	298.8	55	22	①の2	100	55	27.3	—	55	17	27.7	8.1	8.1	0.296
315	313.8	55	22	①の2	100	55	27.3	—	55	17	27.7	8.8	8.8	0.355
355	353.8	55	22	①の2	100	55	27.3	—	55	17	27.7	9.3	9.3	0.510
360	358.8	55	22	①の2	100	55	27.3	—	55	17	27.7	9.7	9.7	0.547
400	398.8	55	22	①の2	100	55	27.3	—	55	17	27.7	11.0	11.0	0.800
450	448.8	55	22	①の2	100	55	27.3	—	55	18	27.7	12.0	12.0	1.20



備考 1)呼び径の太字はJISサイズを表わします。

呼び方例 PS67×3V-2