



WINGED WIRE CONNECTORS

- UL 486C Listed and CSA 22.2 No 188 Certified.
- Tough thermoplastic, UL 94V-2 flame-retardant shell
- Five color-coded to industry standards
- Socket tools are available for easy installation of wire connectors. Please see page E18



Part Number	Dimensions(mm)				
	A	B	C	D	E
P11	6.40	9.80	18.20	9.00	25.80
P12	7.20	11.60	18.30	9.20	29.00
P13	9.00	13.50	23.00	9.60	31.80
P15	10.00	14.90	25.50	10.00	33.30
P17	12.00	18.80	32.00	13.10	40.00

Part Number	Color	Rating & Wire Range		Pcs/Bag	Pcs/Ctn
P11	Yellow	600V Max Temp. 105°C (221°F)	No.18-No.10 AWG. Max.3 #12 Min.2 #18	500	5,000
P12	Tan	600V Max Temp. 105°C (221°F)	No.22-No.8 AWG. Max.4 #12 Min.3 #22	500	5,000
P13	Red	600V Max Temp. 105°C (221°F)	No.18-No.8 AWG. Max.5 #12 Min.3 #16	500	5,000
P15	Grey	600V Max Temp. 105°C (221°F)	No.18-No.8 AWG. Max.3 #10 Min.3 #14 w/1#18	250	2,500
P17	Blue	600V Max Temp. 105°C (221°F)	No.14-No.6 AWG. Max.3 #8 w/1#12 Min.2 #10 w/1#12	100	1,500

E