


90° Large Radius Y

(Abbreviation : LT-VU-LT)



DV Fittings

Code No. 2155

Unit : mm

Nominal Dia.	Z ₁	Z ₂	Z ₃	L ₁	L ₂	L ₃	Standards
40	52	23	52	74	45	74	JIS K 6739
50	66	26	66	91	51	91	
50× 40	52	23	57	77	48	79	
65	90	33	90	125	68	125	
65× 40	52	24	66	87	59	88	
65× 50	66	27	74	101	62	99	
75	100	30	100	140	70	140	
75× 40	52	25	71	92	65	93	
75× 50	66	29	79	106	69	104	
75× 65	90	32	95	130	72	130	
100	128	45	128	178	95	178	
100× 40	52	28	82	102	78	104	
100× 50	66	32	90	116	82	115	
100× 65	90	36	107	140	86	142	
100× 75	100	33	110	150	83	150	
125	140	50	140	205	115	205	
125× 65	90	38	120	155	103	155	
125× 75	100	42	124	165	107	164	
125×100	128	52	140	193	117	190	
150	170	65	170	250	145	250	
150× 65	90	42	130	170	122	165	
150× 75	100	45	135	180	125	175	
150×100	128	53	152	208	133	202	
150×125	140	60	152	220	140	217	

VU-DV Fittings


Code No. 2255

Unit : mm

Nominal Dia.	Z ₁	Z ₂	Z ₃	L ₁	L ₂	L ₃	Standards
50	66	26	66	91	51	91	AS38
75	100	30	100	140	70	140	
75× 50	66	29	79	106	69	104	
100	128	45	128	178	95	178	
100× 50	66	32	90	116	82	115	
100× 75	100	33	110	150	83	150	
125	140	50	140	205	115	205	
150	170	65	170	250	145	250	
150×125	140	60	152	220	140	217	
200	196	94	196	301	199	301	
200×100	128	52	176	233	157	226	M
200×150	170	57	196	275	162	276	

45° Y

(Abbreviation : Y-VU-Y)



DV Fittings

Code No. 2157

Unit : mm

Nominal Dia.	Z ₁	Z ₂	Z ₃	L ₁	L ₂	L ₃	Standards
40	12	58	62	34	80	84	JIS K 6739
Ⓢ40× 30	6	50	58	28	72	76	
50	20	72	78	45	97	103	
50× 40	8	62	70	33	87	92	
65	20	92	98	55	127	133	
65× 40	-1	72	82	34	107	104	
65× 50	8	80	88	43	115	113	
75	26	106	115	66	146	155	
75× 40	-6	78	92	34	118	114	
75× 50	3	86	98	43	126	123	
75× 65	14	98	106	54	138	141	
100	32	134	144	82	184	194	
100× 40	-14	96	112	36	146	134	
100× 50	-8	98	118	42	148	143	
100× 65	3	110	125	53	160	160	
100× 75	19	118	132	69	168	172	
125	38	172	175	103	237	240	
125×100	19	150	171	84	215	221	
150	44	204	210	124	284	290	
150×100	6	165	185	86	245	235	

VU-DV Fittings

Code No. 2257

Unit : mm

Nominal Dia.	Z ₁	Z ₂	Z ₃	L ₁	L ₂	L ₃	Standards	
50	20	72	78	45	97	103	AS38	
75	26	106	115	66	146	155		
75× 50	3	86	98	43	126	123		
100	32	134	144	82	184	194		
100× 50	-8	98	118	42	148	143		
100× 75	19	118	132	69	168	172		
125	38	172	175	103	237	240		
150	44	204	210	124	284	290		
200	42	258	268	147	363	373		AS12
200×100	-15	200	218	90	305	268		M
200×150	7	224	243	112	329	323		

Note The Ⓢ mark indicates that the product is manufactured by Maezawa Kasei Industries Co., Ltd.