

輕少荷重
경소하중
MINIMAL LOAD

CF

하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CF 35×35	35	19	35	5.60	17.5	98	15.7	88	14.0	78
40			4.90	20.0	18.0		16.0			
45			4.36	22.5	20.2		18.0			
50			3.92	25.0	22.5		20.0			
55			3.56	27.5	24.7		22.0			
60			3.26	30.0	27.0		24.0			
65			3.02	32.5	29.2		26.0			
70			2.80	35.0	31.5		28.0			
75			2.61	37.5	33.7		30.0			
80			2.45	40.0	36.0		32.0			
90			2.17	45.0	40.5		36.0			
100			1.96	50.0	45.0		40.0			
125			1.57	62.5	56.2		50.0			
150			1.30	75.0	67.5		60.0			
175			1.12	87.5	78.7		70.0			
200			0.98	100.0	90.0		80.0			
CF 40×40			40	22	40		6.38		20.0	
45	5.67	22.5			20.2	18.0				
50	5.12	25.0			22.5	20.0				
55	4.64	27.5			24.7	22.0				
60	4.26	30.0			27.0	24.0				
65	3.93	32.5			29.2	26.0				
70	3.65	35.0			31.5	28.0				
75	3.40	37.5			33.7	30.0				
80	3.20	40.0			36.0	32.0				
90	2.84	45.0			40.5	36.0				
100	2.56	50.0			45.0	40.0				
125	2.04	62.5			56.2	50.0				
150	1.70	75.0			67.5	60.0				
175	1.46	87.5			78.7	70.0				
200	1.28	100.0			90.0	80.0				
225	1.13	112.5			101.2	90.0				
250	1.02	125.0			112.5	100.0				
275	0.93	137.5	123.7	110.0						
300	0.85	150.0	135.0	120.0						
CF 50×50	50	27.5	50	8.00	25.0	200	22.5	180	20.0	160
55			7.27	27.5	24.7		22.0			
60			6.66	30.0	27.0		24.0			
65			6.15	32.5	29.2		26.0			
70			5.71	35.0	31.5		28.0			
75			5.33	37.5	33.7		30.0			
80			5.00	40.0	36.0		32.0			
90			4.44	45.0	40.5		36.0			
100			4.00	50.0	45.0		40.0			
125			3.20	62.5	56.2		50.0			
150			2.66	75.0	67.5		60.0			
175			2.28	87.5	78.7		70.0			
200			2.00	100.0	90.0		80.0			
225			1.78	112.5	101.2		90.0			
250			1.60	125.0	112.5		100.0			
275			1.45	137.5	123.7		110.0			
300			1.33	150.0	135.0		120.0			
350	1.14	175.0	157.5	140.0						
400	1.00	200.0	180.0	160.0						
450	0.89	225.0	202.5	180.0						
500	0.80	250.0	225.0	200.0						