

中荷重
중하중
MEDIUM LOAD



하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CM 35×35	35	17.5	35	21.87	11.2	245	10.1	220	9.0	196
40			40	19.14	12.8		11.5		10.2	
45			45	17.01	14.4		13.0		11.5	
50			50	15.31	16.0		14.4		12.8	
55			55	13.92	17.6		15.8		14.1	
60			60	12.76	19.2		17.3		15.4	
65			65	11.77	20.8		18.7		16.6	
70			70	10.93	22.4		20.2		17.9	
75			75	10.20	24.0		21.6		19.2	
80			80	9.57	25.6		23.0		20.5	
90			90	8.50	28.8		25.9		23.0	
100			100	7.65	32.0		28.8		25.6	
125			125	6.12	40.0		36.0		32.0	
150			150	5.10	48.0		43.2		38.4	
175			175	4.37	56.0		50.4		44.8	
200			200	3.82	64.0		57.6		51.2	
CM 40×40	40	20	40	25.02	12.8	320	11.5	288	10.2	256
45			45	22.26	14.4		13.0		11.5	
50			50	20.00	16.0		14.4		12.8	
55			55	18.15	17.6		15.8		14.1	
60			60	16.60	19.2		17.3		15.4	
65			65	15.40	20.8		18.7		16.6	
70			70	14.28	22.4		20.2		17.9	
75			75	13.34	24.0		21.6		19.2	
80			80	12.50	25.6		23.0		20.5	
90			90	11.11	28.8		25.9		23.0	
100			100	10.00	32.0		28.8		25.6	
125			125	8.00	40.0		36.0		32.0	
150			150	6.66	48.0		43.2		38.4	
175			175	5.71	56.0		50.4		44.8	
200			200	5.00	64.0		57.6		51.2	
225			225	4.44	72.0		64.8		57.6	
250	250	4.00	80.0	72.0	64.0					
275	275	3.64	88.0	79.2	70.4					
300	300	3.33	96.0	86.4	76.8					
CM 50×50	50	25	50	31.25	16.0	500	14.4	450	12.8	400
55			55	28.41	17.6		15.8		14.1	
60			60	26.04	19.2		17.3		15.4	
65			65	24.04	20.8		18.7		16.6	
70			70	22.32	22.4		20.2		17.9	
75			75	20.83	24.0		21.6		19.2	
80			80	19.53	25.6		23.0		20.5	
90			90	17.36	28.8		25.9		23.0	
100			100	15.62	32.0		28.8		25.6	
125			125	12.50	40.0		36.0		32.0	
150			150	10.41	48.0		43.2		38.4	
175			175	8.92	56.0		50.4		44.8	
200			200	7.81	64.0		57.6		51.2	
225			225	6.94	72.0		64.8		57.6	
250			250	6.25	80.0		72.0		64.0	
275			275	5.68	88.0		79.2		70.4	
300	300	5.20	96.0	86.4	76.8					
350	350	4.46	112.0	100.8	89.6					