

高變形  
高변형  
HIGH DEFLECTION

CR

하중 荷重 ±10%  
직각도 直角度 3° 以下  
자유장 自由長 50m/m 以下 ±0.5m/m  
55m/m 以上 ± 1%

品名 품명 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	密着長 밀착장(mm) Solid Length	定數 정수(kgf/mm) spring constant	100萬(0.3million)	
						變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CR 17×25	17	10.5	25	10.0	1.51	12.5	20.0
30			30	12.0	1.26	15.0	
35			35	14.0	1.08	17.5	
40			40	16.0	0.94	20.0	
45			45	18.0	0.84	22.5	
50			50	20.0	0.76	25.0	
55			55	22.0	0.69	27.5	
60			60	24.0	0.63	30.0	
65			65	26.0	0.58	32.5	
70			70	28.0	0.54	35.0	
75			75	30.0	0.50	37.5	
80			80	32.0	0.47	40.0	
90			90	36.0	0.42	45.0	
100			100	40.0	0.38	50.0	
125			125	50.0	0.30	62.5	
150	150	60.0	0.25	75.0			
CR 21×30	21	13.5	30	12.0	2.00	15.0	30
35			35	14.0	1.71	17.5	
40			40	16.0	1.50	20.0	
45			45	18.0	1.33	22.5	
50			50	20.0	1.20	25.0	
55			55	22.0	1.09	27.5	
60			60	24.0	1.00	30.0	
65			65	26.0	0.92	32.5	
70			70	28.0	0.86	35.0	
75			75	30.0	0.80	37.5	
80			80	32.0	0.75	40.0	
90			90	36.0	0.67	45.0	
100			100	40.0	0.60	50.0	
125			125	50.0	0.48	62.5	
150			150	60.0	0.40	75.0	
175	175	70.0	0.34	87.5			
200	200	80.0	0.30	100.0			
CR 26×30	26	16.5	30	12.0	2.74	15.0	40
35			35	14.0	2.35	17.5	
40			40	16.0	2.06	20.0	
45			45	18.0	1.83	22.5	
50			50	20.0	1.64	25.0	
55			55	22.0	1.49	27.5	
60			60	24.0	1.37	30.0	
65			65	26.0	1.26	32.5	
70			70	28.0	1.17	35.0	
75			75	30.0	1.10	37.5	
80			80	32.0	1.03	40.0	
90			90	36.0	0.91	45.0	
100			100	40.0	0.82	50.0	
110			110	44.0	0.75	55.0	
125			125	50.0	0.66	62.5	
150	150	60.0	0.55	75.0			
175	175	70.0	0.47	87.5			
200	200	80.0	0.41	100.0			