



Semi-Automatic Cutting Machine

IK-93 HAWK

Outstanding mobility and ease of operation resulting in high-quality "Hand-guided cutting".



Overview

IK-93 Hawk is a semi-automatic cutting machine that has been developed primarily for the purpose of high quality straight line cutting by hand guided with smooth operation and running.

Designed after thoroughly checking of the operability. Easy to operate even in the curved cutting, Inside or Outside radius, by the improved position of the grip and the speed adjustment dial.

Feature

- Gas and Speed adjustment, and Clutch operation can be performed by only one hand.
- Easy operation by the tracer guidance.
- Forward and Backward movement available.
- Holders are available in 4 types, Rack type, Screw type, and 2 types for Bevel Cutting.
- Several options available, as Straight Cutting Rail, Circle Cutting Attachment.

IK-93 HAWK - Main Specification

Cutting Thickness	5 - 30mm
Bevel Cut. Angle	0 - 45°
Traveling Speed	100 - 1000mm/min
Speed Control	Dial Adjustment
Length	380mm
Wheel Width	100mm
Weight	7.5kg
Heat Shield	Double Insulation Plate
Cutting Tip	102 (ACE) or 106 (LPG)

Main components and Accessories

- Cutting Machine Body [IK-93 HAWK]
- Power Cable (5M)
- Instruction Manual
- Single Torch Set
- Cutting Tip 102 (ACE) or 106 (LPG) #0,1,2