

Coated Abrasives

HARD DISK2



【Applications】

- Grinding and deburring metals in general, smoothing weld seams of steel, pre-grinding and scouring off rust before plating or painting, and removing paint.

【Features & Benefits】

- Standard flap disk using plastic back plate.
- Has two different hole types followed by two different sizes (O.D. x Hole).

Maximum Allowable Rotation: : 13,000min⁻¹
 〈Packing〉 Large box (Small box x Quantity) : 100(10x10)

Size (mm) (O.D. x Hole)	Grit size	Abrasive		Remarks
		AA	ZN	
100×16(15)	40	-	DPB0031	
	60	DPB0002	DPB0032	
	80	DPB0003	DPB0033	
	100	DPB0004	-	
	120	DPB0005	-	
	180	DPB0007	-	
	240	DPB0008	-	

Maximum Allowable Rotation: : 13,000min⁻¹
 〈Packing〉 Large box (Small box x Quantity) : 100(10x10)

Size (mm) (O.D. x Hole)	Grit size	Abrasive		Remarks
		AA	ZN	
100× Screw-on (M10)	40	DPB0011	DPB0026	
	60	DPB0012	DPB0027	
	80	DPB0013	DPB0028	
	100	DPB0014	--	
	120	DPB0015	-	
	240	DPB0018	-	
	320	DPB0019	-	
	400	DPB0020	-	

Rubber Disc



【Applications】

- Grinding, and deburring metals in general, smoothing weld seams of steel, pre-grinding and scouring off rust before plating or painting, and removing paint.

【Features & Benefits】

- Depressed center wheel, having unique elasticity and great polishing performance.
- One-step polish and finish metals with less noise and vibration due to rubber bond and its unique elasticity.
- Results in better surface finish than our other flexible depressed center wheels.

Maximum Allowable Rotation: : 13,000min⁻¹
 〈Packing〉 Large box (Small box x Quantity) : 50(5x10)

Size (mm) (O.D. x Thk. x Hole)	Grit size	Abrasive	Remarks
		WA	
100×6×15	80	DRD0002	
	120	DRD0003	
	220	DRD0005	
	320	DRD0006	