


ロッキングキー LS, LK


Locking Key LS, LK

RoHS指令適合品



LS

材表 ノブ knob : 艶消し黒色ナイロン樹脂PA6 (ガラス繊維強化)
Glass-fiber Nylon resin
ネジ screw : 鋼材SUM22L・三価クロメート Steel Trivalent Chromate



LK

材 ノブ knob : 艶消し黒色ナイロン樹脂PA6 (ガラス繊維強化)
Glass-fiber Nylon resin
ネジ screw : 黄銅C3604B brass

Unit : mm

品番	M	L	D	D1	H	h	(g)
LS- 4× 6	M 4×P0.7	6	20	9.5	11	0.4	4
LS- 4×10		10					
LS- 5×10	M 5×P0.8	10	26	11.0	13		6
LS- 5×16		16					7
LS- 6×10	M 6×P1.0	10	32	13.0	15		8
LS- 6×16		16					10
LS- 6×25	M 8×P1.25	25	40	15.5	17		12
LS- 8×25		25					16
LS- 8×40		40					20
LS- 8×16-B	M 8×P1.25	16	40	15.5	17		15
LS- 8×25-B		25					16
LS- 8×40-B		40					22
LS-10×20	M10×P1.5	20	40	15.5	17		25
LS-10×30		30					27
LS-10×40		40					31

Unit : mm

品番	M	φ	D	D1	H	h	(g)
LK-4	M 4×P0.7	6	20	9.5	11	0.4	3
LK-5	M 5×P0.8	5	26	11.0	13		4
LK-6	M 6×P1.0	8	32	13.0	15		7
LK-8-A	M 8×P1.25						40
LK-8-B			10				

注意事項 使用温度 max80°C min-20°C