



HG60A

● Order No. Example



- Chain No.60
- Chain Pitch (P)19.05mm
- Roller Link Inner Width (W)12.70mm
- Roller Outside Diameter (Dr)11.91mm
- Tooth Width (T)11.7 mm

m Carbon Structural Steel
h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum			
HG 60A	10H	70	61.65	14	15	0.27		
	11H	76	67.62	14	15	0.30		
	12H	83	73.60	14	15	0.38		
	13H	89	79.60	14	15	0.45		
	14H	95	85.61	16	17	0.50		
	15H	101	91.62	16	17	0.60		
	16H	107	97.65	16	17	0.65		
	17H	113	103.67	16	17	0.75		
	18H	119	109.71	16	17	0.84		
	19H	126	115.74	16	17	0.93		
	20H	132	121.78	16	17	1.05		
	21H	138	127.82	16	17	1.15		
	22H	144	133.86	16	17	1.25		
	23H	150	139.90	16	17	1.40		
	24H	156	145.95	18	19	1.50		
	25H	162	151.99	18	19	1.62		
	26H	168	158.04	18	19	1.78		
	27H	174	164.09	18	19	1.90		
	28H	180	170.14	18	19	2.05		
	29H	187	176.20	18	19	2.20		