



NK60-2B



Order No. Example

NK60-2B 15



Ground Specification

Welded Specification

- Chain No.60-2
- Chain Pitch (P)19.05mm
- Roller Link Inner Width (W)12.70mm
- Roller Outside Diameter (Dr)11.91mm
- Tooth Width (T)11.3 mm (M)34.1mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum Maximum							
NK 60-2B	10	70	61.65	13	14	20	35	50	Ground Specification High-frequency Hardened Teeth	Carbon Structural Steel		
	11	76	67.62	13	14	25	44	50			0.90	
	12	83	73.60	13	14	30	50	50			1.00	
	13	89	79.60	16	17	35	57	50			1.20	
	14	95	85.61	16	17	42	64	56			1.40	
	15	101	91.62	16	17	46	70	56			1.80	
	16	107	97.65	16	17	51	76	56			2.10	
	17	113	103.67	16	17	55	82	56			2.50	
	18	119	109.71	18	19	60	88	56			2.60	
	19	126	115.74	18	19	63	94	56			3.20	
	20	132	121.78	18	19	66	100	56			3.70	
	21	138	127.82	18	19	66	100	56			4.20	
	22	144	133.86	18	19	66	100	56			4.40	
	23	150	139.90	20	21	66	100	56			4.90	
Ground Specification	24	156	145.95	20	21	80	120	56	Carbon Structural Steel	4.70		
	25	162	151.99	20	21	80	120	56		6.00		
	26	168	158.04	20	21	80	120	56		6.40		
	27	174	164.09	20	21	80	120	56		6.80		
	28	180	170.14	20	21	80	120	56		7.30		
	29	187	176.20	20	21	80	120	56		7.80		
	30	193	182.25	20	21	89	130	56		8.20		
										9.00		