



Plastic Chain & Sprocket

Order No. Example

CE400T

Chain No.





40EPT

60EPT

CE400T

Chain used in shipping of lightweight, small goods that makes use of the characteristics of plastics, self-lubrication, and quietness.

Item Name	 Material	 Surface Treatment	Operating Temperature
Chain	Polyacetal Resin	-	-5°C
Pin	CE400T	Common Steel	UniChrome Plating (trivalent)
	40/60EPT	SUS304	-

Chain No.	Pitch P	C	W	W1	H	h1	h2	d	Ap-prox. Weight kg/m	Unit		¥
										Link Quantity	m	Unit
CE 400T	12.7	14.4	32	-	12.7	6.4	6.3	4	0.55	240	3	
40 EPT	12.7	-	20	7.95	12.7	6.7	6	4	0.32	240	3	
60 EPT	19.05	-	30	12.7	17.3	8.8	8.5	6	0.72	160	3	

Dedicated Sprocket

Order No. Example


CE400B 16 D20

Type No. of Teeth Shaft Hole Dimensions
Sprocket No.



* Because dimensional cutting is not available for chains, they are purchased as units.



Precautions



(Shaft Hole Complete Product B-Type)

(Prepared Hole Product B-Type)

- Chain in Use No.CE400
- Chain Pitch (P)12.7 mm
- Roller Link Inner Width ... (W) 7.95mm
- Roller Outside Diameter ... (Dr) 7.95mm
- Tooth Width (T) 7.0 mm (M)21.4mm (C)14.4mm

 Carbon Structural Steel
 UniChrome Plating

Outer Diameter Do	Pitch Diameter Dp	Boss		a	Weight kg	Sprocket No.		Shaft Hole Diameter d			¥		
		BD	BL			Type	No. of Teeth	φD ^{H7} Shaft Hole Complete Product	Prepared Hole Product	Minimum	Maximum	Shaft Hole Complete Product	Prepared Hole Product
68	65.10	50	35	6	0.6	CE400B	16	20 25 30	16	18	30		

Shaft Hole Machined Specification

φD ^{H7}	Keyway bxt2	Set Screw M
18 - 22	6 x 2.8	6
24 - 30	8 x 3.3	8



Chain No. and Quantity
Sprocket No. Shaft Hole Dimensions and Quantity



Same-day shipping
Postage