

Flexible terminal block **TEN and TEU Series**

TEN series assembly completion part

No. of pins	Type name	250V, 1.25mm ² [10A], M3×6±, screw type				General mass (g)	Type name	600V, 2mm ² [20A], M3.5×7±, screw type				General mass (g)	Type name	600V, 3.5mm ² [30A], M4×8±, screw type				General mass (g)
		A	B	C	D			A	B	C	D			A	B	C	D	
2	TEN 7 02	34	B=24,		9.5	TEN 8 02	36	B=29,		14	TEN 11 02	42	B=33,		23.5			
3	TEN 7 03	41	C=16,		13	TEN 8 03	44	C=20,		19	TEN 11 03	53	C=21.5,		32			
4	TEN 7 04	48	D=6		16.5	TEN 8 04	52	D=6.7		24	TEN 11 04	64	D=9.6		40.5			
5	TEN 7 05	55			20	TEN 8 05	60			29	TEN 11 05	75			49			
6	TEN 7 06	62			23.5	TEN 8 06	68			34	TEN 11 06	86			57.5			
7	TEN 7 07	69			27	TEN 8 07	76			39	TEN 11 07	97			66			
8	TEN 7 08	76			30.5	TEN 8 08	84			44	TEN 11 08	108			74.5			
9	TEN 7 09	83			34	TEN 8 09	92			49	TEN 11 09	119			83			
10	TEN 7 10	90			37.5	TEN 8 10	100			54	TEN 11 10	130			91.5			
11	TEN 7 11	97			41	TEN 8 11	108			59	TEN 11 11	141			100			
12	TEN 7 12	104			44.5	TEN 8 12	116			64	TEN 11 12	152			108.5			
13	TEN 7 13	111			48	TEN 8 13	124			69	TEN 11 13	163			117			
14	TEN 7 14	118			51.5	TEN 8 14	132			74	TEN 11 14	174			125.5			
15	TEN 7 15	125			55	TEN 8 15	140			79	TEN 11 15	185			134			
16	TEN 7 16	132			58.5	TEN 8 16	148			84	TEN 11 16	196			142.5			
17	TEN 7 17	139			62	TEN 8 17	156			89	TEN 11 17	207			151			
18	TEN 7 18	146			65.5	TEN 8 18	164			94	TEN 11 18	218			159.5			
19	TEN 7 19	153			69	TEN 8 19	172			99	TEN 11 19	229			168			
20	TEN 7 20	160			72.5	TEN 8 20	180			104	TEN 11 20	240			176.5			

Remark: With cover and name sticker.

TEU series assembly completion part

No. of pins	Type name	600V, 2mm ² [20A], M3.5×7±, up-screw type				General mass (g)	Type name	600V, 3.5mm ² [30A], M4×8±, up-screw type				General mass (g)	Type name	600V, 8mm ² [50A], M5×10±, up-screw type				General mass (g)
		A	B	C	D			A	B	C	D			A	B	C	D	
2	TEU 8 02	36	B=32.6,		20.5	TEU 11 02	42	B=36.5,		30.5	TEU 14 02	52	B=44.5,		69			
3	TEU 8 03	44	C=28,		28	TEU 11 03	53	C=30.5,		42	TEU 14 03	66	C=41,		97			
4	TEU 8 04	52	D=6.7		35.5	TEU 11 04	64	D=9.6		53.5	TEU 14 04	80	D=12.3		125			
5	TEU 8 05	60			43	TEU 11 05	75			65	TEU 14 05	94			153			
6	TEU 8 06	68			50.5	TEU 11 06	86			76.5	TEU 14 06	108			181			
7	TEU 8 07	76			58	TEU 11 07	97			88	TEU 14 07	122			209			
8	TEU 8 08	84			65.5	TEU 11 08	108			99.5	TEU 14 08	136			237			
9	TEU 8 09	92			73	TEU 11 09	119			111	TEU 14 09	150			265			
10	TEU 8 10	100			80.5	TEU 11 10	130			122.5	TEU 14 10	164			293			
11	TEU 8 11	108			88	TEU 11 11	141			134	TEU 14 11	178			321			
12	TEU 8 12	116			95.5	TEU 11 12	152			145.5	TEU 14 12	192			349			
13	TEU 8 13	124			103	TEU 11 13	163			157	TEU 14 13	206			377			
14	TEU 8 14	132			110.5	TEU 11 14	174			168.5	TEU 14 14	220			405			
15	TEU 8 15	140			118	TEU 11 15	185			180	TEU 14 15	234			433			
16	TEU 8 16	148			125.5	TEU 11 16	196			191.5	TEU 14 16	248			461			
17	TEU 8 17	156			133	TEU 11 17	207			203	TEU 14 17	262			489			
18	TEU 8 18	164			140.5	TEU 11 18	218			214.5	TEU 14 18	276			517			
19	TEU 8 19	172			148	TEU 11 19	229			226	TEU 14 19	290			545			
20	TEU 8 20	180			155.5	TEU 11 20	240			237.5	TEU 14 20	304			573			

Remark: With cover and name sticker.



Line-up
Clutch Lock
Terminal Blocks
PLC Interface
Terminal Blocks
Rail Type
Terminal Blocks
Assembly
Terminal Blocks
Special Purpose
Terminal Blocks
Terminal
Block Accessories