

● Order No. Example

TB 210L 075
TBU | | |
 Type | Belt Nominal Length | Belt Nominal Width

Material	Belt Nominal Width
TB=Rubber	050=(12.7mm), 075=(19.1mm) 100=(25.4mm), 150=(38.1mm)
TBU=Polyurethane	050=(12.7mm), 075=(19.1mm) 100=(25.4mm), 150=(38.1mm)

Type		Belt Nominal Length	No. of Teeth	Belt Pitch Circumference (mm)	¥				¥		
TB	TBU				Rubber				Polyurethane		
					050	075	100	150	050	075	100
○		109L	29	276.23							
○	○	124L	33	314.33							
○		135L	36	342.90							
○	○	150L	40	381.00							
○	○	165L	44	419.10							
○	○	187L	50	476.25							
○	○	210L	56	533.40							
○	○	225L	60	571.50							
○	○	240L	64	609.60							
○	○	255L	68	647.70							
○	○	270L	72	685.80							
○		277L	74	704.85							
○	○	285L	76	723.90							
○	○	300L	80	762.00							
○		320L	85	809.63							
○	○	322L	86	819.15							
○		334L	89	847.73							
○		337L	90	857.25							
○	○	345L	92	876.30							
○		360L	96	914.40							
○	○	367L	98	933.45							
○		375L	100	952.50							
○		382L	102	971.55							
○	○	390L	104	990.60							
○		394L	105	1000.13							
○	○	420L	112	1066.80							
○		427L	114	1085.85							
○	○	450L	120	1143.00							
○	○	480L	128	1219.20							
○	○	510L	136	1295.40							
○		525L	140	1333.50							
○	○	540L	144	1371.60							
○		548L	146	1390.65							
○		581L	155	1476.38							
○	○	600L	160	1524.00							
○		630L	168	1600.20							
○		653L	174	1657.35							
○		660L	176	1676.40							
○		697L	186	1771.65							
○		731L	195	1857.38							