

H型寸法一覧表

〈H100A〉 選択可能な材質：鋼材

歯数	寸法(mm)							適応軸穴径 (mm) ※軸穴公差H7																	定価(円/個)					
	PD	OD	LA	W	H	F	M	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	S1	S2	S3
14	56.60	55.22				61	41																					6,550	7,170	8,520
15	60.64	59.27				65	50																					6,750	7,390	8,780
16	64.68	63.31				69	50																					6,950	7,610	9,040
18	72.77	71.39				78	58																					7,000	7,670	9,100
19	76.81	75.44				83	63																					7,200	7,880	9,360
20	80.85	79.48				86	66																					7,800	8,500	9,980
21	84.89	83.52				90	73																					8,000	8,720	10,240
22	88.94	87.56				93	75																					8,100	8,830	10,290
24	97.02	95.65	33	28	2.5	105	84																					9,500	10,360	11,690
25	101.06	99.69				108	84																					10,000	10,900	12,100
26	105.11	103.73				112	90																					10,100	11,010	12,930
28	113.19	111.82				118	90																					10,500	11,450	13,440
30	121.28	119.90				126	100																					10,900	11,880	13,730
32	129.36	127.99				136	118																					11,500	12,540	14,490
34	137.45	136.07				146	128																					12,500	13,630	15,500
36	145.53	144.16				152	134																					12,900	14,060	15,870
40	161.70	160.33				168	150																					13,500	14,720	17,820

〈H100B〉 選択可能な材質：鋼材

歯数	寸法(mm)											適応軸穴径 (mm) ※軸穴公差H7																	定価(円/個)							
	PD	OD	LA	LB	W	H	K	D	F	M		14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	S1	S2	S3		
14	56.60	55.22										38	61	41																				7,100	7,770	9,220
15	60.64	59.27										46	65	50																				7,200	7,880	9,340
16	64.68	63.31										46	69	50																				7,300	7,990	9,470
18	72.77	71.39										54	78	58																				7,600	8,320	9,780
19	76.81	75.44										55	83	63																				7,700	8,430	9,910
20	80.85	79.48										56	86	66																				8,300	9,050	10,420
21	84.89	83.52										58	90	73																				8,600	9,370	10,790
22	88.94	87.56										58	93	75																				8,800	9,590	10,860
24	97.02	95.65	33	28	2.5							62	105	84																				10,600	11,550	12,850
25	101.06	99.69										66	108	84																				11,200	12,210	13,450
26	105.11	103.73										70	112	90																				11,400	12,430	14,380
28	113.19	111.82										74	118	90																				12,100	13,190	14,760
30	121.28	119.90										74	126	100																				12,700	13,840	15,480
32	129.36	127.99										78	136	118																				13,700	14,930	16,680
34	137.45	136.07										82	146	128																				13,800	15,040	16,660
36	145.53	144.16										82	152	134																				14,100	15,370	17,140
40	161.70	160.33										88	168	150																				15,300	16,680	19,810

〈H150A〉 選択可能な材質：鋼材

歯数	寸法(mm)							適応軸穴径 (mm) ※軸穴公差H7																	定価(円/個)						
	PD	OD	LA	W	H	F	M	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	S1	S2	S3	
14	56.60	55.22				61	41																						7,200	7,880	9,360
15	60.64	59.27				65	50																						7,400	8,100	9,620
16	64.68	63.31				69	50																						7,450	8,160	9,690
18	72.77	71.39				78	58																						7,800	8,540	10,140
19	76.81	75.44				83	63																						8,100	8,870	10,530
20	80.85	79.48				86	66																						8,500	9,270	11,050
21	84.89	83.52				90	73																						8,900	9,700	11,390
22	88.94	87.56				93	75																						9,100	9,920	11,650
24	97.02	95.65	45	40	2.5	105	84																						10,500	11,450	13,020
25	101.06	99.69				108	84																						10,700	11,660	13,270
26	105.11	103.73				112	90																						11,000	11,990	13,640
28	113.19	111.82				118	90																						11,700	12,750	14,510
30	121.28	119.90				126	100																						12,100	13,190	15,490
32	129.36	127.99				136	118																						14,100	15,370	17,630
34	137.45	136.07				146	128																						15,300	16,680	18,820
36	145.53	144.16				152	134																						16,600	18,090	20,250
40	161.70	160.33				168	150																						19,200	20,930	24,000

※青塗部はタップ長さが不足する為、標準のセットスクリーが付属されます。(P3参照)

●製品コード例

