

H型寸法一覧表

〈H150B〉 選択可能な材質：鋼材

歯数	寸法(mm)								適応軸穴径 (mm) ※軸穴公差H7																定価(円/個)													
	PD	OD	LA	LB	W	H	K	D	F	M	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	S1	S2	S3					
14	56.60	55.22									38	61	41																			7,500	8,210	9,750				
15	60.64	59.27									46	65	50				16	17	18	19	20	22	24	25								8,000	8,760	10,400				
16	64.68	63.31									46	69	50				16	17	18	19	20	22	24	25								8,100	8,870	10,530				
18	72.77	71.39									54	78	58				16	17	18	19	20	22	24	25	28	30						8,600	9,420	11,010				
19	76.81	75.44									55	83	63				16	17	18	19	20	22	24	25	28	30						8,800	9,640	11,260				
20	80.85	79.48									56	86	66				16	17	18	19	20	22	24	25	28	30	32					9,200	10,030	11,590				
21	84.89	83.52									58	90	73				16	17	18	19	20	22	24	25	28	30	32					9,600	10,460	12,000				
22	88.94	87.56									58	93	75									20	22	24	25	28	30	32				10,000	10,900	12,500				
24	97.02	95.65	45			40	2.5				62	105	84									20	22	24	25	28	30	32	35	38		11,900	12,970	14,400				
25	101.06	99.69									66	108	84									20	22	24	25	28	30	32	35	38	40		12,200	13,300	14,760			
26	105.11	103.73									70	112	90									20	22	24	25	28	30	32	35	38	40	42		12,500	13,630	15,130		
28	113.19	111.82									74	118	90									20	22	24	25	28	30	32	35	38	40	42		13,300	14,500	16,360		
30	121.28	119.90									74	126	100									20	22	24	25	28	30	32	35	38	40	42		13,800	15,040	16,970		
32	129.36	127.99									78	136	118									20	22	24	25	28	30	32	35	38	40	42	45		14,700	16,020	18,080	
34	137.45	136.07									82	146	128									20	22	24	25	28	30	32	35	38	40	42	45		14,900	16,240	18,330	
36	145.53	144.16									82	152	134									20	22	24	25	28	30	32	35	38	40	42	45	48		15,200	16,570	18,700
40	161.70	160.33									88	168	150									20	22	24	25	28	30	32	35	38	40	42	45	48	50	16,800	18,310	21,500

〈H200A〉 選択可能な材質：鋼材

歯数	寸法(mm)								適応軸穴径 (mm) ※軸穴公差H7																定価(円/個)											
	PD	OD	LA	W	H	F	M		14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	S1	S2	S3					
14	56.60	55.22									61	41																					7,600	8,320	9,880	
15	60.64	59.27									65	50																						8,000	8,760	10,400
16	64.68	63.31									69	50																						8,050	8,810	10,470
18	72.77	71.39									78	58																						8,500	9,310	11,050
19	76.81	75.44									83	63																						8,900	9,750	11,570
20	80.85	79.48									86	66																						9,700	10,570	12,420
21	84.89	83.52									90	73																						10,000	10,900	12,800
22	88.94	87.56									93	75																						10,200	11,120	13,060
24	97.02	95.65	59			54	2.5				105	84																						12,400	13,520	15,130
25	101.06	99.69									108	84																						12,900	14,060	15,740
26	105.11	103.73									112	90																						13,000	14,170	16,640
28	113.19	111.82									118	90																						13,200	14,390	16,900
30	121.28	119.90									126	100																						15,800	17,220	19,750
32	129.36	127.99									136	118																						17,500	19,080	21,350
34	137.45	136.07									146	128																						18,600	20,270	22,320
36	145.53	144.16									152	134																						22,300	24,310	26,310
40	161.70	160.33									168	150																						24,500	26,710	29,890

〈H200B〉 選択可能な材質：鋼材

歯数	寸法(mm)								適応軸穴径 (mm) ※軸穴公差H7																定価(円/個)												
	PD	OD	LA	LB	W	H	K	D	F	M	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	S1	S2	S3				
14	56.60	55.22									38	61	41				16	17	18	19	20													8,100	8,870	10,530	
15	60.64	59.27									46	65	50				16	17	18	19	20	22	24	25										8,500	9,310	11,050	
16	64.68	63.31									46	69	50				16	17	18	19	20	22	24	25										8,800	9,640	11,350	
18	72.77	71.39									54	78	58				16	17	18	19	20	22	24	25	28	30								9,200	10,070	11,870	
19	76.81	75.44									55	83	63				16	17	18	19	20	22	24	25	28	30								9,600	10,510	12,380	
20	80.85	79.48									60	86	66																						10,500	11,450	13,340
21	84.89	83.52									65	90	73																						10,800	11,770	13,610
22	88.94	87.56									70	93	75																						11,000	11,990	13,860
24	97.02	95.65	59			54	2.5				74	105	84																						13,300	14,500	16,090
25	101.06	99.69									74	108	84																						13,900	15,150	16,680
26	105.11	103.73									78	112	90																						14,300	15,590	18,020
28	113.19	111.82									78	118	90																						14,700	16,020	18,520
30	121.28	119.90									86	126	100																						17,900	19,510	21,840
32	129.36	127.99									92	136	118																						19,000	20,710	22,990
34	137.45	136.07									98	146	128																						19,500	21,260	23,400
36	145.53	144.16									98	152	134																						19,900	21,690	23,880
40	161.70	160.33									104	168	150																						22,000	23,980	27,720

※青塗部はタップ長さが不足する為、標準のセットスクリーンが付属されます。(P3参照)

●製品コード例

