

# Super Torque Timing Belt <S2M>

## ● Order No. Example

**STB 40 S2M100**  
**STBU**

Type Belt Nominal Width Belt Nominal Length

Material	Belt Nominal Width
STB=Rubber	40=(4mm), 60=(6mm) 100=(10mm)
STBU=Polyurethane	40=(4mm), 60=(6mm) 100=(10mm)

Type		Belt Nominal Length	No. of Teeth	Belt Pitch Circumference (mm)	¥			¥		
STB	STBU				Rubber			Polyurethane		
					40	60	100	40	60	100
○		S2M76	38	76						
○		S2M78	39	78						
○	○	S2M80	40	80						
○		S2M88	44	88						
○	○	S2M90	45	90						
○	○	S2M100	50	100						
○	○	S2M112	56	112						
○		S2M116	58	116						
○		S2M118	59	118						
○		S2M122	61	122						
○		S2M124	62	124						
○	○	S2M126	63	126						
○		S2M128	64	128						
○		S2M130	65	130						
○		S2M132	66	132						
○		S2M134	67	134						
○	○	S2M138	69	138						
○	○	S2M140	70	140						
○		S2M142	71	142						
○	○	S2M144	72	144						
○		S2M152	76	152						
○	○	S2M160	80	160						
○	○	S2M164	82	164						
○	○	S2M166	83	166						
○	○	S2M172	86	172						
○		S2M176	88	176						
○		S2M180	90	180						
○		S2M186	93	186						
○	○	S2M190	95	190						
○	○	S2M194	97	194						
○	○	S2M200	100	200						
○		S2M204	102	204						
○	○	S2M210	105	210						
○	○	S2M212	106	212						
○		S2M214	107	214						
○	○	S2M218	109	218						
○	○	S2M220	110	220						
○	○	S2M224	112	224						
○	○	S2M230	115	230						
○		S2M234	117	234						
○	○	S2M236	118	236						
○	○	S2M240	120	240						