


NV800-SEW NV800-HEW




NV800-SEW

Model		NV800-SEW	NV800-HEW	
Number of poles		3		
Rated operational voltage Ue (V AC)		100-440 Multi-voltage type		
Rated current In (A)		400-800 adjustable		
High-speed type	Rated current sensitivity IΔn (mA)	-		
	Max. operating time at 5IΔn (s)	-		
Time-delay type	Rated current sensitivity IΔn (mA)	100 · 200 · 500 Selectable		
	Max. operating time at 5IΔn (s)	0.45 · 1.0 · 2.0 Selectable		
	Max. inertial non-operating time at 2IΔn (s)	0.1 · 0.5 · 1.0		
Earth-leakage indication system		Button		
Rated short-circuit breaking capacity (kA) IEC 60947-2 (Icu/Ics) EN 60947-2	AC	440V	42/42	65/65
		400V	50/50	70/70
		230V	85/85	100/100
Standard attached parts (Front connection)		Mounting screw: M6x35 (4pcs) Insulation barrier: (2pcs)		


Operating Characteristics




Earth Leakage Tripping Characteristics



Internal Accessories



Current Reducing Curve



External Accessories

Accessories	Type name	Accessories	Type name
Operating handle	F	Auxiliary handle	HT HT-4SW
	V	Terminal cover	Large TC-L TCL-8SW3
Mechanical interlock	MI	Skeleton	TTC TTC-8SW3
		Rear	BTC BTC-8SW3
Electrical operation device		Handle lock device	HL HL-4SW
			HL-S HLS-8SW
		Electrical operation device	(*1)

Note *1 Specify the operation method and voltage. Order in combination with the breaker unit.

Internal Wiring Diagram

