

C Controller Interface Module Utility

Installation Instructions

■ Introduction

Thank you for purchasing C Controller Interface Module Utility. This document explains how to install and uninstall C Controller Interface Module Utility ^(Note-1). Please read carefully before installing the product to your personal computer.

(Note-1): C Controller Interface Module Utility includes API library for the Q173SCCF, and test tool that can confirm the development of control application and operation for Mitsubishi Electric C Controller Interface Module Q173SCCF.

■ Product Makeup

Model name	Product name	Quantity
SW1DNC-QSCCF-B	C Controller Interface Module Utility CD-ROM	1
	Installation Instructions (This manual)	1
	Software license agreement	1

Precautions

- We do not guarantee any commercially available Microsoft Windows Operating System products that are introduced in this manual.
- This software's copyright is owned by Mitsubishi Electric Corporation.
- This software requires one license per computer to be purchased. However, only API library can be used for royalty free.
- This product (including manual) can be used under the Software License Agreement only.
- We do not take any responsibilities for the consequences of operating this product (including manual).
- User's Manual in the CD-ROM is a PDF file. To View the PDF file, Adobe® Reader® is required. Download from the Adobe Systems Incorporated website.

⚠ Acknowledgements

- Reprinting or reproducing the part or all the contents of this document in any form for any purpose without the permission of Mitsubishi Electric Corporation is strictly forbidden.
- Although we have made the utmost effort to follow the revisions of the software and hardware, in some cases, unsynchronized matter may occur.
- The information in this document may be subject to change without notice.
- We do not take any responsibility for the virus infection and network failure caused by temporary deactivation of antivirus or security software.

■ Operating Environment

Item	Contents	
Personal computer main body	Personal computer	Microsoft® Windows® supported personal computer
	OS	Microsoft Windows 10 English version (64-bit/32-bit) Microsoft Windows 8.1 English version (64-bit/32-bit) Microsoft Windows 8 English version (64-bit/32-bit) Microsoft Windows 7 English version (64-bit/32-bit) [Service Pack 1] Microsoft Windows Vista® English version (32-bit) [Service Pack 2] Microsoft Windows XP® English version (32-bit) [Service Pack 3]
	CPU	Desktop PC : Intel® Celeron® Processor 2.8GHz or higher Laptop PC : Intel Pentium® M Processor 1.7GHz or higher
	Required memory	1GB or more recommended (For 32-bit edition) 2GB or more recommended (For 64-bit edition)
Available hard disk space	When installing C Controller Interface Module Utility: Available hard disk space: 1GB or more When operating C Controller Interface Module Utility: Available virtual memory space: 512MB or more	
Disk drive	CD-ROM supported disk drive	
Monitor	Resolution 1024 x 768 pixels or higher	
Communication interfaces	USB port	
API library	C Controller Module : Q24DHCCPU-V Operating system : VxWorks 6.8.1 Programming development environment: CW Workbench, Wind River Workbench 3.2	

Precautions

- (1) The following functions cannot be used. This product may not perform properly when these functions are used.
- Activating the application with Windows compatible mode
 - Simplified user switch-over
 - Remote desktop
 - Large fonts (Detail settings of screen property)
 - DPI setting other than that of the normal size (Detail settings of screen property)
 - Windows XP Mode
 - Windows Touch or Touch
 - Modern UI Style
 - Client Hyper-V