

# S8M寸法一覧表

### <S8M0150A> 選択可能な材質：鋼材

歯数	寸法(mm)								適応軸穴径(mm) ※軸穴公差H7													定価(円/個)								
	PD	OD	LA	W	H	F	M														S1	S2	S3							
														18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	55
18	45.84	44.46	24	17	3.5														7,150	7,830	9,180									
19	48.38	47.01																	7,220	7,900	9,270									
20	50.93	49.56																	7,280	7,970	9,350									
21	53.48	52.1																	7,350	8,050	9,440									
22	56.02	54.65																	7,400	8,100	9,500									
24	61.12	59.74																	7,530	8,240	9,660									
25	63.66	62.29																	7,610	8,330	9,760									
26	66.21	64.84																	7,690	8,410	9,860									
28	71.3	69.93																	8,170	8,940	10,480									
30	76.39	75.02																	8,450	9,250	10,840									
32	81.49	80.12																	8,690	9,510	11,140									
34	86.58	85.21																	9,140	10,000	11,710									
36	91.67	90.3																	9,470	10,360	12,130									
38	96.77	95.39																	10,520	11,470	13,380									
40	101.86	100.49																	11,270	12,290	14,330									
44	112.05	110.67														12,350	13,470	15,700												
48	122.23	120.86														13,440	14,640	17,050												
50	127.32	125.95														14,620	15,930	18,540												
60	152.79	151.42														19,260	20,960	24,370												

### <S8M0150B> 選択可能な材質：鋼材

歯数	寸法(mm)										適応軸穴径(mm) ※軸穴公差H7													定価(円/個)								
	PD	OD	LA	LB	W	H	K	D	F	M														S1	S2	S3						
											12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	55
18	45.84	44.46	24	17	3.5	15														7,530	8,240	9,660										
19	48.38	47.01																		7,590	8,300	9,730										
20	50.93	49.56																		7,650	8,370	9,810										
21	53.48	52.1																		7,710	8,440	9,890										
22	56.02	54.65																		7,750	8,480	9,940										
24	61.12	59.74																		7,860	8,600	10,070										
25	63.66	62.29																		8,010	8,760	10,260										
26	66.21	64.84																		8,140	8,900	10,430										
28	71.3	69.93																		8,410	9,200	10,770										
30	76.39	75.02																		8,560	9,360	10,960										
32	81.49	80.12																		9,050	9,890	11,580										
34	86.58	85.21																		9,320	10,190	11,920										
36	91.67	90.3																		9,590	10,480	12,260										
38	96.77	95.39																		10,790	11,760	13,690										
40	101.86	100.49																		11,630	12,670	14,750										
44	112.05	110.67	44														12,830	13,980	16,270													
48	122.23	120.86															13,750	14,960	17,390													
50	127.32	125.95															15,360	16,720	19,430													
60	152.79	151.42														20,510	22,310	25,900														

### <S8M0250A> 選択可能な材質：鋼材

歯数	寸法(mm)								適応軸穴径(mm) ※軸穴公差H7													定価(円/個)													
	PD	OD	LA	W	H	F	M														S1	S2	S3												
														12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	48	50	55
18	45.84	44.46	35	28	3.5														7,900	8,650	10,140														
19	48.38	47.01																	7,970	8,720	10,220														
20	50.93	49.56																	8,030	8,790	10,300														
21	53.48	52.1																	8,160	8,930	10,460														
22	56.02	54.65																	8,260	9,040	10,590														
24	61.12	59.74																	8,490	9,290	10,880														
25	63.66	62.29																	8,590	9,400	11,010														
26	66.21	64.84																	8,690	9,510	11,140														
28	71.3	69.93																	9,100	9,950	11,660														
30	76.39	75.02																	9,300	10,170	11,910														
32	81.49	80.12																	9,730	10,640	12,460														
34	86.58	85.21																	10,790	11,800	13,820														
36	91.67	90.3																	11,130	12,170	14,250														
38	96.77	95.39																	12,160	13,260	15,450														
40	101.86	100.49																	12,820	13,970	16,280														
44	112.05	110.67														13,890	15,130	17,620																	
48	122.23	120.86														15,460	16,840	19,590																	
50	127.32	125.95														16,770	18,260	21,240																	
60	152.79	151.42														22,690	24,690	28,690																	

※青塗部はタップ長さが不足する為、準標準のセットスクリューが付属されます。(P.3参照)

### ●製品コード例



- S1：鋼材+表面処理無し
- S2：鋼材+黒染
- S3：鋼材+無電解ニッケルメッキ
- 20：ブリー歯数
- S8M：ブリー歯形
- 0150：ブリー呼び幅 (使用ベルト幅mm×10)
- A：ブリー形状
- F - 18：軸穴径(mm) 例) φ7は07と記入
- T2：フランジ P.3表2参照
- K：キー溝(JS9公差) P.3表3参照