



CLASS 150

Unit 単位 : mm

| Nominal Size 呼び径 | | Outside Diameter 外径 | Thick-ness 厚さ | Length thru Hub 全長 | | | Diam. of Hub ハブ元の径 | Raised Face Diam. 座径 | Corner Radius of Bore 隅半径 | Depth of Socket ソケット深さ | Counter-Bore 取付面の径 | Thread Length ネジ有効深さ | Bolt Holes ボルト穴 | | |
|---------------------|-------|------------------------|------------------|--------------------|----------|-----|-----------------------|-------------------------|------------------------------|---------------------------|---|-------------------------|----------------------------|--------------|-------------|
| | | | | WN | SO SW TR | LJ | | | | | | | Bolt Circle Diam. 中心円の径 | Number 穴数 | Diam. 穴径 |
| A | B | O | t | Y1 | Y2 | Y3 | X | R | r1 | D | B4 | Q | C | H | |
| 15 | 1/2 | 89 | 11.2 | 47.8 | 16 | | 30.0 | 35.1 | 3 | 10 | | 16 | 60.5 | 4 | 16 |
| 20 | 3/4 | 99 | 12.7 | 52.3 | 16 | | 38.0 | 42.9 | 3 | 11 | | 16 | 69.8 | 4 | 16 |
| 25 | 1 | 108 | 14.3 | 55.6 | 18 | | 49.5 | 50.8 | 3 | 13 | | 18 | 79.2 | 4 | 16 |
| 32 | 1 1/4 | 117 | 15.8 | 57.2 | 21 | | 58.5 | 63.5 | 5 | 14 | Chamfered to major diam. of thread at 45° | 21 | 88.9 | 4 | 16 |
| 40 | 1 1/2 | 127 | 17.6 | 62.0 | 22 | | 65.0 | 73.2 | 6 | 16 | | 22 | 98.6 | 4 | 16 |
| 50 | 2 | 152 | 19.1 | 63.5 | 25 | | 77.5 | 91.9 | 8 | 18 | | 25 | 120.6 | 4 | 19 |
| 65 | 2 1/2 | 178 | 22.4 | 69.8 | 28 | | 90.5 | 104.6 | 8 | 19 | | 28 | 139.7 | 4 | 19 |
| 80 | 3 | 190 | 23.9 | 69.8 | 30 | | 108 | 127.0 | 10 | 21 | | 30 | 152.4 | 4 | 19 |
| 90 | 3 1/2 | 216 | 23.9 | 71.4 | 32 | | 122 | 139.7 | 10 | — | | 32 | 177.8 | 8 | 19 |
| 100 | 4 | 229 | 23.9 | 76.2 | 33 | | 135 | 157.2 | 11 | — | | 33 | 190.5 | 8 | 19 |
| 125 | 5 | 254 | 23.9 | 88.9 | 37 | | 164 | 185.7 | 11 | — | | 37 | 215.9 | 8 | 22 |
| 150 | 6 | 279 | 25.4 | 88.9 | 40 | | 192 | 215.9 | 13 | — | | 40 | 241.3 | 8 | 22 |
| 200 | 8 | 343 | 28.5 | 101.6 | 44 | | 246 | 269.7 | 13 | — | | 44.4 | 298.4 | 8 | 22 |
| 250 | 10 | 406 | 30.3 | 101.6 | 49 | | 305 | 323.8 | 13 | — | 49.3 | 362.0 | 12 | 26 | |
| 300 | 12 | 483 | 31.8 | 114.3 | 56 | | 365 | 381.0 | 13 | — | 55.6 | 431.8 | 12 | 26 | |
| 350 | 14 | 535 | 35.1 | 127.0 | 57 | 79 | 400 | 412.8 | 13 | — | 57.2 | 476.2 | 12 | 29 | |
| 400 | 16 | 595 | 36.6 | 127.0 | 64 | 87 | 457 | 469.9 | 13 | — | 63.5 | 539.8 | 16 | 29 | |
| 450 | 18 | 635 | 39.7 | 139.7 | 68 | 97 | 505 | 533.4 | 13 | — | 68.3 | 577.8 | 16 | 32 | |
| 500 | 20 | 700 | 43.0 | 144.5 | 73 | 103 | 559 | 584.2 | 13 | — | 73.2 | 635.0 | 20 | 32 | |
| 600 | 24 | 815 | 47.8 | 152.4 | 83 | 111 | 663 | 692.2 | 13 | — | 82.6 | 749.3 | 20 | 35 | |

CLASS 300

Unit 単位 : mm

| Nominal Size 呼び径 | | Outside Diameter 外径 | Thick-ness 厚さ | Length thru Hub 全長 | | | Diam. of Hub ハブ元の径 | Raised Face Diam. 座径 | Corner Radius of Bore 隅半径 | Depth of Socket ソケット深さ | Counter-Bore 取付面の径 | Thread Length ネジ有効深さ | Bolt Holes ボルト穴 | | |
|---------------------|-------|------------------------|------------------|--------------------|----------|-----|-----------------------|-------------------------|------------------------------|---------------------------|-----------------------|-------------------------|----------------------------|--------------|-------------|
| | | | | WN | SO SW TR | LJ | | | | | | | Bolt Circle Diam. 中心円の径 | Number 穴数 | Diam. 穴径 |
| A | B | O | t | Y1 | Y2 | Y3 | X | R | r1 | D | B4 | Q | C | H | |
| 15 | 1/2 | 95 | 14.3 | 52.3 | 22 | | 38.0 | 35.1 | 3 | 10 | 23.5 | 15.7 | 66.5 | 4 | 16 |
| 20 | 3/4 | 117 | 15.8 | 57.2 | 25 | | 48.0 | 42.9 | 3 | 11 | 29.0 | 15.7 | 82.6 | 4 | 19 |
| 25 | 1 | 124 | 17.6 | 62.0 | 27 | | 54.0 | 50.8 | 3 | 13 | 36.0 | 17.5 | 88.9 | 4 | 19 |
| 32 | 1 1/4 | 133 | 19.1 | 65.0 | 27 | | 63.5 | 63.5 | 5 | 14 | 44.5 | 20.6 | 98.6 | 4 | 19 |
| 40 | 1 1/2 | 155 | 20.6 | 68.3 | 30 | | 70.0 | 73.2 | 6 | 16 | 50.5 | 22.4 | 114.3 | 4 | 22 |
| 50 | 2 | 165 | 22.4 | 69.8 | 33 | | 84.0 | 91.9 | 8 | 18 | 63.5 | 28.4 | 127.0 | 8 | 19 |
| 65 | 2 1/2 | 190 | 25.4 | 76.2 | 38 | | 100 | 104.6 | 8 | 19 | 76.0 | 31.8 | 149.4 | 8 | 22 |
| 80 | 3 | 210 | 28.5 | 79.2 | 43 | | 117 | 127.0 | 10 | 21 | 92.0 | 31.8 | 168.1 | 8 | 22 |
| 90 | 3 1/2 | 229 | 30.3 | 81.0 | 44 | | 133 | 139.7 | 10 | — | 105.0 | 36.6 | 184.2 | 8 | 22 |
| 100 | 4 | 254 | 31.8 | 85.9 | 48 | | 146 | 157.2 | 11 | — | 118.0 | 36.6 | 200.2 | 8 | 22 |
| 125 | 5 | 279 | 35.1 | 98.6 | 51 | | 178 | 185.7 | 11 | — | 145.0 | 42.9 | 235.0 | 8 | 22 |
| 150 | 6 | 318 | 36.6 | 98.6 | 52 | | 206 | 215.9 | 13 | — | 171.0 | 46.0 | 269.7 | 12 | 22 |
| 200 | 8 | 381 | 41.2 | 111.3 | 62 | | 260 | 269.7 | 13 | — | 222.0 | 50.8 | 330.2 | 12 | 26 |
| 250 | 10 | 444 | 47.8 | 117.3 | 67 | 95 | 321 | 323.8 | 13 | — | 276.0 | 55.6 | 387.4 | 16 | 29 |
| 300 | 12 | 520 | 50.8 | 130.0 | 73 | 102 | 375 | 381.0 | 13 | — | 329.0 | 60.5 | 450.8 | 16 | 32 |
| 350 | 14 | 585 | 53.9 | 142.7 | 76 | 111 | 425 | 412.8 | 13 | — | 360.0 | 63.5 | 514.4 | 20 | 32 |
| 400 | 16 | 650 | 57.2 | 146.0 | 83 | 121 | 483 | 469.9 | 13 | — | 411.0 | 68.3 | 571.5 | 20 | 35 |
| 450 | 18 | 710 | 60.5 | 158.8 | 89 | 130 | 533 | 533.4 | 13 | — | 462.0 | 69.8 | 628.6 | 24 | 35 |
| 500 | 20 | 775 | 63.5 | 162.1 | 95 | 140 | 587 | 584.2 | 13 | — | 513.0 | 73.2 | 685.8 | 24 | 35 |
| 600 | 24 | 915 | 69.9 | 168.1 | 106 | 152 | 702 | 692.2 | 13 | — | 614.0 | 82.6 | 812.8 | 24 | 42 |

Note: Regarding the flange bore B1, B2, & B3 and the diameter A of hub at bevel, refer to "Flange bore and diameter of hub at bevel" of page 52.

注: 内径 B1, B2, B3 とハブ先の径 A は、52頁の「フランジ内径とハブ先の径」を参照のこと。