



# External Cutting

## SDJE

### SDJEL1616H15



Type [\[Expand\]](#)

Type [\[Expand\]](#)

- Screw-on type
- High rake and good sharpness.

The actual product may differ from the displayed image.

For details, please check the dimensions below.

Diameter (Unit)	
Hand	L
Stock	●
Unit of Length	M
<b>B</b>	16
<b>KAPR</b>	93°
<b>LF</b>	100
<b>LH</b>	27
<b>WF</b>	20
<b>H</b>	16
<b>HF</b>	16
Peripheral effective cutting edge count: ZEFP	1
Insert Number	DE__1504

[Show more](#)

Stock
●:Inventory maintained.
□:Non stock, produced to order only.
▲:Inventory maintained. To be replaced by new products.
★:Inventory maintained in Japan.

2D Model (DXF)	
CAD data name	Download
SDJEL1616H15	

3D Detail Model (STP,STL)	
CAD data name	Download
SDJEL1616H15	

3D Light Model (STP,STL)		
CAD data name	RE	Download
SDJEL1616H15_MR0_4	0.4	