




SPP-N/SPP-W Plastic Screw - Hex Nuts / Washers - PP

WEB Selection Tool
 WEB CAD Download
 Chemical-proof



● Material/Finish

RoHS Compliant

SPP-N / SPP-W

Main body	PP (Polypropylene) / Milky White
Heat Resistance Temperature*	65°C

*Teflon is a registered trademark of DuPont.

**This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

- PP plastic has excellent resistance to chemicals such as strong acids and organic solvents.
- It is used as a replacement for vinyl chloride type plastic screws.
- The properties and precautions of plastic screws → P.724
- Application

FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, and chemical plants

SPP-N Hex Nuts

Unit : mm

Part Number	M	B	T	Mass (g)	Qty per pack*1
SPP-M4-N	M4	7	3.2	0.092	20
SPP-M5-N	M5	8	4	0.14	20
SPP-M6-N	M6	10	5	0.28	10
SPP-M8-N	M8	13	6.5	0.63	10
SPP-M10-N	M10	17	8	1.3	10

*1 The minimum order quantity is 1 piece. → P.794

SPP-W Washers

Unit : mm

Part Number	d	D	t	Nominal	Mass (g)	Qty per pack*1
SPP-4-W	4.3	9	0.8	4	0.036	20
SPP-5-W	5.3	10	1	5	0.051	20
SPP-6-W	6.4	12.5	1.6	6	0.13	10
SPP-8-W	8.4	17	1.6	8	0.25	10
SPP-10-W	10.5	21	2	10	0.47	10

*1 The minimum order quantity is 1 piece. → P.794

- Part number specification

SPP-M4-N

1

Order in number of packs.
The minimum order quantity is 1 piece. → P.794

Individual Sales → P.794	Cleanroom Wash & Packaging → P.792	Screw Length Adjustment → P.796	Vibration Resistant → P.795	Modification process for captive use → P.791
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available