




● 50 ~ 68HRC の焼き入れ鋼の高効率加工が可能です。

This drill meets high efficiency drilling of hardened material.
(50~68HRC)



商品紹介
アクアドリルハード 10頁



LIST 9548

オーダ方法

AQDH 直径

切削条件 Drilling Condition ▶▶A-213

単位 (Unit): mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
2.0	12	44	3	●	2,480
2.1	12	44	3	●	2,660
2.2	13	45	3	□	-
2.3	13	45	3	□	-
2.4	14	46	3	□	-
2.5	14	46	3	●	2,660
2.6	14	46	3	●	2,660
2.7	16	48	3	□	-
2.8	16	48	3	□	-
2.9	16	48	3	□	-
3.0	16	48	3	●	2,660
3.1	18	50	4	□	-
3.2	18	50	4	□	-
3.3	18	50	4	□	-
3.4	20	52	4	●	7,170
3.5	20	52	4	●	7,170
3.6	20	52	4	□	-
3.7	20	52	4	□	-
3.8	22	54	4	□	-
3.9	22	54	4	□	-
4.0	22	54	4	●	7,570
4.1	22	66	6	□	-
4.2	22	66	6	□	-
4.3	24	68	6	●	8,090
4.4	24	68	6	□	-
4.5	24	68	6	●	8,090
4.6	24	68	6	□	-
4.7	24	68	6	□	-
4.8	26	70	6	□	-
4.9	26	70	6	□	-
5.0	26	70	6	●	8,640
5.1	26	70	6	●	9,150
5.2	26	70	6	□	-
5.3	26	70	6	□	-
5.4	28	72	6	□	-
5.5	28	72	6	●	9,150
5.6	28	72	6	□	-
5.7	28	72	6	□	-
5.8	28	72	6	□	-
5.9	28	72	6	□	-
6.0	28	72	6	●	9,570
6.1	31	75	8	□	-
6.2	31	75	8	□	-
6.3	31	75	8	□	-
6.4	31	75	8	□	-
6.5	31	75	8	●	9,570
6.6	31	75	8	□	-
6.7	31	75	8	□	-
6.8	34	78	8	□	-
6.9	34	78	8	●	10,200
7.0	34	78	8	●	10,200
7.1	34	78	8	□	-
7.2	34	78	8	□	-
7.3	34	78	8	□	-
7.4	34	78	8	□	-
7.5	34	78	8	●	10,800
7.6	37	81	8	□	-
7.7	37	81	8	□	-
7.8	37	81	8	□	-
7.9	37	81	8	□	-

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
8.0	37	81	8	●	11,300
8.1	37	87	10	□	-
8.2	37	87	10	□	-
8.3	37	87	10	□	-
8.4	37	87	10	□	-
8.5	37	87	10	●	12,000
8.6	40	90	10	●	12,500
8.7	40	90	10	□	-
8.8	40	90	10	□	-
8.9	40	90	10	□	-
9.0	40	90	10	●	12,500
9.1	40	90	10	□	-
9.2	40	90	10	□	-
9.3	40	90	10	□	-
9.4	40	90	10	□	-
9.5	40	90	10	●	13,200
9.6	43	93	10	□	-
9.7	43	93	10	□	-
9.8	43	93	10	□	-
9.9	43	93	10	□	-
10.0	43	93	10	●	13,800
10.1	43	100	12	□	-
10.2	43	100	12	□	-
10.3	43	100	12	●	14,400
10.4	43	100	12	□	-
10.5	43	100	12	●	14,400
10.6	43	100	12	□	-
10.7	47	104	12	□	-
10.8	47	104	12	□	-
10.9	47	104	12	□	-
11.0	47	104	12	●	15,000
11.1	47	104	12	□	-
11.2	47	104	12	□	-
11.3	47	104	12	□	-
11.4	47	104	12	□	-
11.5	47	104	12	●	15,600
11.6	47	104	12	□	-
11.7	47	104	12	□	-
11.8	47	104	12	□	-
11.9	51	108	12	□	-
12.0	51	108	12	●	16,100

□は特定代理店在庫品です。
Available for Japan customers only.

低炭素鋼 軟鋼	炭素鋼 合金鋼	プレハードン鋼 高合金鋼	調質鋼	焼入鋼	
SS400, S10C ~150HB	S45C, SCM440 ~225HB	SUJ, NAK ~275HB	SKD, SKH 30~40HRC	Hardened Steels	
×	×	×	×	40~50HRC	50~65HRC
ステンレス鋼			耐熱合金	鋳鉄	アルミ合金 銅・銅合金
SUS304	SUS420	Ti/Ni Alloys	FC/FCD	AC/ADC	Cu
×	×	×		×	×

◎:最過 Excellent ○:適用 Good ×:不適 Not Used 無印 (No mark):推奨しません Not recommended