


●鋼からステンレス鋼そしてアルミまで、高能率加工ができます。高い穴位置精度が得られます。

This drill having short length is suitable for high-speed drilling of most material from Carbon Steels and Stainless Steels to Aluminum.



切削条件 Drilling Condition ▶▶▶ A-236

LIST 6568P

オーダ方法

GSS 直径

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
1.0	8	33	●	908
1.1	9	34	●	859
1.2	10	35	●	819
1.3	10	35	●	859
1.4	12	37	●	859
1.5	12	37	●	859
1.6	13	39	●	663
1.7	13	39	●	714
1.8	15	42	●	663
1.9	15	42	●	663
2.0	16	44	●	663
2.1	16	44	●	940
2.2	18	47	●	940
2.3	18	47	●	849
2.4	20	50	●	940
2.5	20	50	●	849
2.6	20	50	●	849
2.7	22	54	●	849
2.8	22	54	●	893
2.9	22	54	●	849
3.0	22	54	●	849
3.1	24	57	●	1,010
3.2	24	57	●	1,010
3.3	24	57	●	1,010
3.4	26	61	●	1,010
3.5	26	61	●	1,010
3.6	26	61	●	1,150
3.7	26	61	●	1,150
3.8	29	65	●	1,150
3.9	29	65	●	1,150
4.0	29	65	●	1,150
4.1	29	65	●	1,300
4.2	29	65	●	1,300
4.3	32	69	●	1,300
4.4	32	69	●	1,300
4.5	32	69	●	1,300
4.6	32	69	●	1,450
4.7	32	69	●	1,450
4.8	35	74	●	1,450
4.9	35	74	●	1,450
5.0	35	74	●	1,450
5.1	35	74	●	1,610
5.2	35	74	●	1,610
5.3	35	74	●	1,610
5.4	38	80	●	1,610
5.5	38	80	●	1,610
5.6	38	80	●	1,760
5.7	38	80	●	1,760
5.8	38	80	●	1,760
5.9	38	80	●	1,760
6.0	38	80	●	1,760
6.1	42	86	●	1,920
6.2	42	86	●	1,920
6.3	42	86	●	1,920
6.4	42	86	●	1,920
6.5	42	86	●	1,920
6.6	42	86	●	2,050
6.7	42	86	●	2,050
6.8	46	92	●	2,050
6.9	46	92	●	2,050

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
7.0	46	92	●	2,050
7.1	46	92	●	2,220
7.2	46	92	●	2,220
7.3	46	92	●	2,220
7.4	46	92	●	2,220
7.5	46	92	●	2,220
7.6	50	98	●	2,370
7.7	50	98	●	2,370
7.8	50	98	●	2,370
7.9	50	98	●	2,370
8.0	50	98	●	2,370
8.1	50	98	●	2,500
8.2	50	98	●	2,500
8.3	50	98	●	2,500
8.4	50	98	●	2,500
8.5	50	98	●	2,500
8.6	54	105	●	2,660
8.7	54	105	●	2,660
8.8	54	105	●	2,660
8.9	54	105	●	2,660
9.0	54	105	●	2,660
9.1	54	105	●	2,810
9.2	54	105	●	2,810
9.3	54	105	●	2,810
9.4	54	105	●	2,810
9.5	54	105	●	2,810
9.6	58	111	●	2,980
9.7	58	111	●	2,980
9.8	58	111	●	2,980
9.9	58	111	●	3,270
10.0	58	111	●	2,980
10.1	58	111	●	3,630
10.2	58	111	●	3,460
10.3	58	111	●	3,460
10.4	58	111	●	3,630
10.5	58	111	●	3,460
10.6	58	111	●	4,030
10.7	63	119	●	4,030
10.8	63	119	●	4,030
10.9	63	119	●	4,030
11.0	63	119	●	3,660
11.1	63	119	●	4,390
11.2	63	119	●	4,390
11.3	63	119	●	4,390
11.4	63	119	●	4,390
11.5	63	119	●	3,990
11.6	63	119	●	4,770
11.7	63	119	●	4,770
11.8	63	119	●	4,770
11.9	68	127	●	4,770
12.0	68	127	●	4,350
12.1	68	127	●	6,200
12.2	68	127	●	6,200
12.3	68	127	●	6,200
12.4	68	127	●	6,200
12.5	68	127	●	5,620
12.6	68	127	●	6,870
12.7	68	127	●	6,870
12.8	68	127	●	6,870
12.9	68	127	●	6,870

食付性のよい先研ぎ形状のため、状況に応じてセンチもみを省略することもできます。チッピング対策におすすめのドリルです。包装数量は直径 2mm 未満：10本、2mm 以上：1本です。