

SD ストレートシャンクドリル

Straight Shank Drills

●もっとも広い用途で使用されている汎用ドリルです。

This drill is applied for general purpose.




直径 2.0mm 未満の表面は白 (無着色) です。
Less than 2.0mm in the diameter is the bright finishes.

LIST 500

オーダー方法

SD 直径



Dc > 13.0

S形

Dc ≤ 13.0

円すい

切削条件 Drilling Condition A-237

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
0.2	3	19	●	865
0.21	3.5	20	●	1,120
0.22	3.5	20	●	1,120
0.23	3.5	20	●	1,120
0.24	3.5	20	●	1,120
0.25	3.5	20	●	1,040
0.26	3.5	20	●	1,120
0.27	3.5	20	●	1,120
0.28	3.5	20	●	1,120
0.29	3.5	20	●	1,120
0.3	3.5	20	●	543
0.31	5.5	24	●	676
0.32	5.5	24	●	676
0.33	5.5	24	●	676
0.34	5.5	24	●	676
0.35	5.5	24	●	634
0.36	5.5	24	●	676
0.37	5.5	24	●	676
0.38	5.5	24	●	676
0.39	5.5	24	●	676
0.4	5.5	24	●	449
0.41	7.5	27	●	560
0.42	7.5	27	●	560
0.43	7.5	27	●	560
0.44	7.5	27	●	560
0.45	7.5	27	●	527
0.46	7.5	27	●	560
0.47	7.5	27	●	560
0.48	7.5	27	●	560
0.49	7.5	27	●	560
0.5	7.5	30	●	362
0.51	8.5	30	●	468
0.52	8.5	30	●	468
0.53	8.5	30	●	468
0.54	8.5	30	●	468
0.55	8.5	30	●	440
0.56	8.5	30	●	468
0.57	8.5	30	●	468
0.58	8.5	30	●	468
0.59	8.5	30	●	468
0.6	8.5	30	●	366
0.61	10	32	●	457
0.62	10	32	●	457
0.63	10	32	●	457
0.64	10	32	●	457
0.65	10	32	●	426
0.66	10	32	●	457
0.67	10	32	●	457
0.68	10	32	●	457
0.69	10	32	●	457
0.7	10	32	●	337
0.71	11	34	●	421
0.72	11	34	●	421
0.73	11	34	●	421
0.74	11	34	●	421
0.75	11	34	●	396
0.76	11	34	●	421
0.77	11	34	●	421
0.78	11	34	●	421
0.79	11	34	●	421

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
0.8	11	34	●	286
0.81	13	36	●	382
0.82	13	36	●	382
0.83	13	36	●	382
0.84	13	36	●	382
0.85	13	36	●	360
0.86	13	36	●	382
0.87	13	36	●	382
0.88	13	36	●	382
0.89	13	36	●	382
0.9	13	36	●	307
0.91	18	40	●	382
0.92	18	40	●	382
0.93	18	40	●	382
0.94	18	40	●	382
0.95	18	40	●	360
0.96	18	40	●	382
0.97	18	40	●	382
0.98	18	40	●	382
0.99	18	40	●	382
1.0	18	40	●	259
1.01	20	42	●	344
1.02	20	42	●	344
1.03	20	42	●	344
1.04	20	42	●	344
1.05	20	42	●	316
1.06	20	42	●	344
1.07	20	42	●	344
1.08	20	42	●	344
1.09	20	42	●	344
1.1	20	42	●	304
1.11	20	42	●	344
1.12	20	42	●	344
1.13	20	42	●	344
1.14	20	42	●	344
1.15	20	42	●	316
1.16	20	42	●	344
1.17	20	42	●	344
1.18	20	42	●	344
1.19	20	42	●	344
1.2	20	42	●	286
1.21	22	45	●	344
1.22	22	45	●	344
1.23	22	45	●	344
1.24	22	45	●	344
1.25	22	45	●	316
1.26	22	45	●	344
1.27	22	45	●	344
1.28	22	45	●	344
1.29	22	45	●	344
1.3	22	45	●	304
1.31	23	48	●	344
1.32	23	48	●	344
1.33	23	48	●	344
1.34	23	48	●	344
1.35	23	48	●	316
1.36	23	48	●	344
1.37	23	48	●	344
1.38	23	48	●	344
1.39	23	48	●	344