


●生材から焼入材まで幅広く対応できます。仕上げ加工に適しています。

This end mill is suitable for workpiece materials from raw materials to hardened materials, and for finish milling.



切削条件 Milling Condition ▶▶B-217

LIST 9382

オーダ方法

商品記号

商品記号 CODE	外径 Dc	刃長 ℓ	全長 L	シャック径 Ds	在庫 Stock	参考価格 Price
2GS0.2	0.2	0.4	40	4	●	5,350
2GS0.3	0.3	0.6	40	4	●	4,670
2GS0.4	0.4	0.8	40	4	●	4,670
2GS0.5 × 4	0.5	1.25	40	4	●	2,590
2GS0.6	0.6	1.25	40	4	●	3,950
2GS0.7	0.7	1.5	40	4	●	3,870
2GS0.8	0.8	2	40	4	●	2,470
2GS0.9	0.9	2	40	4	●	3,400
2GS1 × 4	1	2.5	40	4	●	2,320
2GS1.1	1.1	2.5	40	4	●	4,350
2GS1.2	1.2	3	40	4	●	2,200
2GS1.3	1.3	3	40	4	●	4,350
2GS1.4	1.4	3	40	4	●	4,350
2GS1.5 × 4	1.5	3.75	40	4	●	2,320
2GS1.6	1.6	4	40	4	●	4,350
2GS1.7	1.7	4	40	4	●	4,350
2GS1.8	1.8	5	40	4	●	2,200
2GS1.9	1.9	5	40	4	●	4,350
2GS2 × 4	2	5	40	4	●	2,320
2GS2.1	2.1	6	40	4	●	5,140
2GS2.2	2.2	6	40	4	●	5,140
2GS2.3	2.3	6	40	4	●	5,140
2GS2.4	2.4	6	40	4	●	5,140
2GS2.5 × 4	2.5	6.25	40	4	●	2,320
2GS2.6	2.6	7	40	4	●	5,140
2GS2.7	2.7	7	40	4	●	5,140
2GS2.8	2.8	7	40	4	●	4,400
2GS2.9	2.9	7	40	4	●	5,140
2GS3 × 6	3	7.5	45	6	●	2,900
2GS3.1	3.1	8	45	6	●	5,230
2GS3.2	3.2	8	45	6	●	5,230
2GS3.3	3.3	8	45	6	●	5,230
2GS3.4	3.4	10	45	6	●	5,230
2GS3.5	3.5	10	45	6	●	4,400
2GS3.6	3.6	10	45	6	●	5,230
2GS3.7	3.7	10	45	6	●	5,230
2GS3.8	3.8	11	45	6	●	5,230
2GS3.9	3.9	11	45	6	●	5,230
2GS4 × 6	4	11	45	6	●	3,040
2GS4.1	4.1	11	45	6	●	5,660
2GS4.2	4.2	11	45	6	●	5,660
2GS4.3	4.3	11	45	6	●	5,660
2GS4.4	4.4	11	45	6	●	5,660
2GS4.5	4.5	11	50	6	●	5,000
2GS4.6	4.6	11	50	6	●	5,660
2GS4.7	4.7	11	50	6	●	5,660
2GS4.8	4.8	13	50	6	●	5,660
2GS4.9	4.9	13	50	6	●	5,660
2GS5	5	13	50	6	●	3,270
2GS5.1	5.1	13	50	6	●	5,880
2GS5.2	5.2	13	50	6	●	5,880
2GS5.3	5.3	13	50	6	●	5,880
2GS5.4	5.4	13	50	6	●	5,880
2GS5.5	5.5	13	50	6	●	5,200
2GS5.6	5.6	13	50	6	●	5,880
2GS5.7	5.7	13	50	6	●	5,880
2GS5.8	5.8	13	50	6	●	5,880
2GS5.9	5.9	13	50	6	●	5,880
2GS6	6	13	50	6	●	3,400
2GS7 × 8	7	16	60	8	●	6,590

単位 (Unit): mm / 円 (¥)

商品記号 CODE	外径 Dc	刃長 ℓ	全長 L	シャック径 Ds	在庫 Stock	参考価格 Price
2GS8	8	19	60	8	●	5,020
2GS9 × 10	9	19	70	10	●	8,820
2GS10	10	22	70	10	●	6,190
2GS11 × 12	11	22	75	12	●	11,500
2GS12	12	26	75	12	●	8,340
2GS13	13	26	75	12	●	17,600
2GS14	14	26	90	16	●	19,600
2GS15	15	26	90	16	●	24,800
2GS16	16	32	90	16	●	25,100
2GS18	18	32	100	20	●	38,900
2GS20	20	38	100	20	●	42,400

単位 (Unit): mm / 円 (¥)

商品記号 CODE	外径 Dc	刃長 ℓ	全長 L	シャック径 Ds	在庫 Stock	参考価格 Price
2GS0.5	0.5	1.25	38	3	●	2,590
2GS1	1	2.5	38	3	●	2,320
2GS1.5	1.5	3.75	38	3	●	2,320
2GS2	2	5	38	3	●	2,320
2GS2.5	2.5	6.25	38	3	●	2,320
2GS3	3	7.5	38	3	●	2,900
2GS4	4	11	45	4	●	3,040

外径 (mm) Dc		許容差 (mm) Tolerance
を超え Above	以下 Up to	
	3	0 ~ -0.015
3	12	0 ~ -0.020
12		0 ~ -0.030

低炭素鋼 軟鋼	炭素鋼 合金鋼	プレハードン鋼 高合金鋼	調質鋼	焼入鋼	
SS400, S10C ~150HB	S45C, SCM440 ~225HB	SUJ, NAK ~275HB	SKD, SKH 30 ~ 40HRC	Hardened Steels 40 ~ 55HRC 55 ~ 65HRC	
◎	◎	◎	◎	◎	
ステンレス鋼	耐熱合金	鋳鉄	アルミ合金	銅・銅合金	グラファイト
SUS304	Ti/Ni Alloys	FC/PCD	AC/ADC	Cu	Graphite
◎	○	○			

◎:最適 Excellent ○:適用 Good ×:不適 Not Used 無印 (No mark):推奨しません Not recommended