


●止まり穴のねじ加工に用いる汎用タップです。

This is a general spiral tap for tapping blind holes.



LIST 6904 NACHI-TDT

オーダ方法

TSP 記号

切削条件 Cutting Condition ▶ C-30

単位 (Unit) : mm / 円 (¥)

記号 Code No.	呼び Thread Size	食付 (P) Lc (P)	等級 TAP Limit	全長 L	ねじ長 ℓ	溝数 Flutes	シャンク径 Ds	首下長さ Ln	首径 dn	形式 Type	在庫 Stock	参考価格 Price
2M0.4	M2 X 0.4	2.5	G3	40	8	3	3	15	2	1	●	1,520
2.3M0.4	M2.3 X 0.4	2.5	G3	42	9.5	3	3	15	2.3	1	●	1,370
2.5M0.45	M2.5 X 0.45	2.5	G3	44	9.5	3	3	16	2.5	1	●	1,200
2.6M0.45	M2.6 X 0.45	2.5	G3	44	9.5	3	3	16	2.6	1	●	1,060
3M0.5	M3 X 0.5	2.5	G6	46	5	3	4	18	2.3	2	●	853
3.5M0.6	M3.5 X 0.6	2.5	G6	48	5	3	4	18	2.7	2	●	917
4M0.7	M4 X 0.7	2.5	G6	52	7	3	5	20	3.05	2	●	815
5M0.8	M5 X 0.8	2.5	G6	60	8	3	5.5	22	3.9	2	●	837
6M1	M6 X 1	2.5	G6	62	10	3	6	25	4.7	2	●	892
6M0.75	M6 X 0.75	2.5	G6	62	10	3	6	25	4.7	2	●	1,210
7M1	M7 X 1	2.5	G6	65	10	3	6.2	26	5.7	3	●	1,170
8M1.25	M8 X 1.25	2.5	G7	70	12	3	6.2	34	6	3	●	1,290
8M1	M8 X 1	2.5	G7	70	12	3	6.2	34	6	3	●	1,620
10M1.5	M10 X 1.5	2.5	G7	75	15	3	7	39	6.8	3	●	1,630
10M1.25	M10 X 1.25	2.5	G7	75	15	3	7	39	6.8	3	●	1,630
10M1	M10 X 1	2.5	G7	75	15	3	7	39	6.8	3	●	2,050
12M1.75	M12 X 1.75	2.5	G8	82	17	3	8.5	43	8.3	3	●	2,270
12M1.5	M12 X 1.5	2.5	G8	82	17	3	8.5	43	8.3	3	●	2,270
12M1.25	M12 X 1.25	2.5	G8	82	17	3	8.5	43	8.3	3	●	2,270
14M2	M14 X 2	2.5	G8	88	20	3	10.5	44	10.3	3	●	3,160
14M1.5	M14 X 1.5	2.5	G8	88	20	3	10.5	44	10.3	3	●	3,160
16M2	M16 X 2	2.5	G8	95	20	3	12.5	50	12.3	3	●	4,220
16M1.5	M16 X 1.5	2.5	G8	95	20	3	12.5	50	12.3	3	●	4,220
18M2.5	M18 X 2.5	2.5	G9	100	25	3	14	56	13.8	3	●	5,760
18M1.5	M18 X 1.5	2.5	G8	100	25	3	14	56	13.8	3	●	5,760
20M2.5	M20 X 2.5	2.5	G9	105	25	4	15	57	14.8	3	●	7,480
20M1.5	M20 X 1.5	2.5	G8	105	25	4	15	57	14.8	3	●	7,480
22M2.5	M22 X 2.5	2.5	G9	115	25	4	17	62	16.8	3	●	9,700
22M1.5	M22 X 1.5	2.5	G8	115	25	4	17	62	16.8	3	●	9,700
24M3	M24 X 3	2.5	G9	120	30	4	19	67	18.8	3	●	12,100
24M1.5	M24 X 1.5	2.5	G8	120	30	4	19	67	18.8	3	●	12,100
27M3	M27 X 3	2.5	G9	130	30	4	20	67	19.8	3	●	17,200
27M1.5	M27 X 1.5	2.5	G8	130	30	4	20	67	19.8	3	●	17,200
30M3.5	M30 X 3.5	2.5	G9	135	35	4	23	72	22.8	3	●	22,000
30M1.5	M30 X 1.5	2.5	G8	135	35	4	23	72	22.8	3	●	22,000

包装数量 Packed quantity

呼び Thread Size	数量 Pcs.
M 2 ~ M10	10
M12 ~ M16	5
M18 ~ M30	1

シャンク四角部寸法

Square portion size of shank

単位 (Unit)

シャンク径 d	シャンク四角部	
	K	Lk
3	2.5	5
4	3.2	6
5	4	7
5.5	4.5	7
6	4.5	7
6.2	5	8
7	5.5	8
8.5	6.5	9
10.5	8	11
12.5	10	13
14	11	14
15	12	15
17	13	16
19	15	18
20	15	18
23	17	20