

Hardmatic HH-300

SERIES 811 — Durometers for Rubber and Plastics Hardness Testing

FEATURES

Digital / Dial Durometers are suitable for testing the nature of the following materials — natural rubber, neoprene, polyesters, P.V.C., leather, nitrite rubber, wax, vinyl, cellulose acetates, glass polystyrene, etc.



Compact Digital
Compact Dial

811-336-10
811-335-10



Long Leg Digital
Long Leg Dial

811-332-10
811-331-10

SPECIFICATIONS

Order No.	Digital	811-330-10	811-336-10	811-336-11	811-332-10	811-338-10	811-338-11	811-334-10
	Dial	811-329-10	811-335-10	811-335-11	811-331-10	811-337-10	811-337-11	811-333-10
Model No.	Digital	HH-330	HH-336	HH-336	HH-332	HH-338	HH-338	HH-334
	Dial	HH-329	HH-335	HH-335	HH-331	HH-337	HH-337	HH-333
Scale		Shore E	Shore A			Shore D		
Applications		Soft Rubber, Sponge, Felt, Hard Foam	Natural rubber, soft elastomers, etc.			Hard elastomers, plastics, hard rubber, ebonite, etc.		
Resolution		0.1 (digital) or 1 (dial)				0.1 (digital) or 1 (dial)		
Range		HA: 10 - 90				HD: 20 - 90		
Standards	ASTM D 2240	—	✓	✓	—	✓	—	✓
	ISO 868	—	✓	✓	—	✓	—	✓
	ISO 7619	—	✓	✓	—	✓	—	✓
	DIN 53 505	—	—	✓	—	—	—	✓
	JIS K 6253	✓	✓	✓	—	✓	—	✓
	JIS K 7215	—	✓	✓	—	✓	—	✓
Pressure foot		44 x 18mm	44 x 18mm	ø18mm		44 x 18mm	ø18mm	
Spring force (mN)		WE=550+HE	WA=550+75HD (HA:Reading 10-90)			WD=444.5HD (HD:Reading 20-90)		
Indenter		Sphere (Tip diameter: 0.79mm)	Blunt taper (Tip diameter: 0.79mm)			Sharp point (Tip curvature: 0.1±0.01mm)		
Tip angle		—	35°±0.25°			30°±0.5°		
Indenter diameter		5mm	1.25mm					
Indenter protrusion		2.5mm						
Functions		Digital: Data hold, Zero -setting, SPC output, Power ON/OFF (Power supply: SR44 x 1pc.) Analog Durometer: Peak retaining hand						
Type		Compact	Compact	Long-leg	Compact	Long-leg		
Dimensions (WxDxH)	Digital	60 x 28.5 x 151	60 x 28.5 x 151mm	60 x 28.5 x 193mm	60 x 28.5 x 151mm	60 x 28.5 x 193mm		
	Dial	56 x 33.5 x 144mm	56 x 33.5 x 144mm	56 x 33.5 x 186mm	56 x 33.5 x 144mm	56 x 33.5 x 186mm		
Mass	Digital	290g	290g	310g	290g	310g		
	Dial	300g	300g	320g	300g	320g		

Technical Data

- Designed in accordance with the ASTM D 2240, ISO868, ISO 7619, DIN 53 505, JIS K 6253, and JIS K 7215 specifications.
- Units are available in both Shore A and Shore D scales, and will test a wide variety of applications.
- The Digital Durometer is provided with data hold function, permitting the operator to make an error-free reading on the LCD screen.
- The Dial Durometer is provided with a peak retaining hand for error-free reading.

