


●鋼からステンレス鋼そしてアルミまで適したコーティングロングドリルです。

This is general coated long drills for deep holes.



オーダ方法

GLTD 直径 × 全長

直径4.0~6.9
在庫品限り

単位 (Unit) : mm

直径 Dc	全長 L	溝長 ℓ	シャंक MT No.	在庫 Stock
4.0	200	125		
4.2	200			
4.3	200			
4.5	200			
4.8	200			
5.0	200			
5.0	250	150		
5.0	300	200		
5.1	200	125		
5.1	250	150		
5.2	200	125		
5.2	250	150		
5.3	200	125		
5.3	250	150		
5.4	200	125		
5.4	250	150		
5.5	200	125		
5.5	250	150		
5.5	300	200		
5.6	200	125		
5.6	250	150		
5.7	200	125		
5.7	250	150		
5.8	200	125		
5.8	250	150		
5.9	200	125		
5.9	250	150		
6.0	200	125		
6.0	250	150		
6.0	300	200		
6.1	200	125		
6.1	250	150		
6.2	200	125		
6.2	250	150		
6.3	200	125		
6.3	250	150		
6.4	200	125		
6.4	250	150		
6.5	200	125		
6.5	250	150		
6.5	300	200		
6.6	200	125		
6.6	250	150		
6.7	200	125		
6.7	250	150		
6.8	200	125		
6.8	250	150		
6.8	300	200		
6.9	200	125		
6.9	250	150		
7.0	200	125		
7.0	250	150		
7.0	300	200		
7.1	200	125		
7.1	250	150		
7.2	200	125		
7.2	250	150		
7.3	200	125		
7.3	250	150		
7.4	200	125		

直径 Dc	全長 L	溝長 ℓ	シャंक MT No.	在庫 Stock
7.4	250	150		
7.5	200	125		
7.5	250	150		
7.5	300	200		
7.6	200	125		
7.6	250	150		
7.7	200	125		
7.7	250	150		
7.8	200	125		
7.8	250	150		
7.9	200	125		
7.9	250	150		
8.0	200	125		
8.0	250	150		
8.0	300	200		
8.0	350	250		
8.0	400	275		
8.0	500	375		
8.0	600	425		
8.1	200	125		
8.1	250	150		
8.1	300	200		
8.2	200	125		
8.2	250	150		
8.2	300	200		
8.3	200	125		
8.3	250	150		
8.3	300	200		
8.4	200	125		
8.4	250	150		
8.4	300	200		
8.5	200	125		
8.5	250	150		
8.5	300	200		
8.5	350	250		
8.5	400	275		
8.5	500	375		
8.5	600	425		
8.6	200	125		
8.6	250	150		
8.6	300	200		
8.7	200	125		
8.7	250	150		
8.7	300	200		
8.8	200	125		
8.8	250	150		
8.8	300	200		
8.9	200	125		
8.9	250	150		
8.9	300	200		
9.0	200	125		
9.0	250	150		
9.0	300	200		
9.0	350	250		
9.0	400	275		
9.0	500	375		
9.0	600	425		
9.1	200	125		
9.1	250	150		
9.1	300	200		

直径 Dc	全長 L	溝長 ℓ	シャंक MT No.	在庫 Stock
9.2	200	125		
9.2	250	150		
9.2	300	200		
9.3	200	125		
9.3	250	150		
9.3	300	200		
9.4	200	125		
9.4	250	150		
9.4	300	200		
9.5	200	125		
9.5	250	150		
9.5	300	200		
9.5	350	250		
9.5	400	275		
9.5	500	375		
9.5	600	425		
9.6	200	125		
9.6	250	150		
9.6	300	200		
9.7	200	125		
9.7	250	150		
9.7	300	200		
9.8	200	125		
9.8	250	150		
9.8	300	200		
9.9	200	125		
9.9	250	150		
9.9	300	200		
10.0	200	125		
10.0	250	150		
10.0	300	200		
10.0	350	250		
10.0	400	275		
10.0	500	375		
10.0	600	425		
10.1	200	125		
10.1	250	150		
10.1	300	200		
10.2	200	125		
10.2	250	150		
10.2	300	200		
10.3	200	125		
10.3	250	150		
10.3	300	200		
10.4	200	125		
10.4	250	150		
10.4	300	200		
10.5	200	125		
10.5	250	150		
10.5	300	200		
10.5	350	250		
10.5	400	275		
10.5	500	375		
10.5	600	425		
10.6	200	125		
10.6	250	150		
10.6	300	200		
10.7	200	125		
10.7	250	150		
10.7	300	200		

□は特定代理店在庫品です。
□ : Available for Japan customers only.