


# NK-9100 For Fuel Tanks (Satisfied the fire law of A)

DN: 40mm(1-1/2") ~ 400mm(16")  
 Length: 500mm ~ 3.2M  
 \*Depending on the DN.  
 Flange Standard: JIS, ANSI, ASME



Threaded Type Flexible Hose


F1

Flange Type Flexible Hose

F2

# NK-9500 For Fire Extinguishing Pumps (Satisfied the fire law of B)

DN: 32mm(1-1/4") ~ 300mm(12") : JIS 10K, #150Lb  
 32mm(1-1/4") ~ 200mm(8") : JIS 20K, #300Lb  
 Length: 190mm ~ 3M  
 Flange Standard: JIS, ANSI, ASME



Fire Law Flexible Hose

F3


Quick Connection Flexible Hose

F4

Flexible Hose for Vacuums

# NK-CT2 For Chemical Tanks

DN: 15mm(1/2") ~ 65mm(2-1/2")  
 Length: 300mm ~ 1400mm  
 \*Depending on the DN.  
 Flange Standard: JIS, ANSI, ASME



① Inner Tube	Fluororesin
② Gasket	Non Asbestos
③ Collar	Stainless Steel
④ Flexible Tube	Stainless Steel
⑤ Braid	Stainless Steel
⑥ Flange	Carbon Steel, Stainless Steel

F5

Flexible Hose with Fluororesin

F6

Other Flexible Hose

F7