



SAD-RF / SADS-RF Screw Adaptor - Fine Threaded Type



WEB Selection Tool WEB CAD Download SUS Stainless steel



- Usage example
In combination with a dimple knob.



- By combining with female screw products such as a lever and knob, this may be used as a fine threaded screw lever or knob.
- For screw fixing, use a pin stopper or anaerobic adhesive agent. If it is repeatedly tightened, a pin stopper is recommended.
- Use a stopper ring to accurately determine the thread length.

- Material/Finish **1** RoHS Compliant

	SAD-RF Made of Steel	SADS-RF Made of Stainless Steel
Thread Part	SUM22 Trivalent Chromate Treatment	SUS303
Stopper Ring	Equivalent to SUS304	Equivalent to SUS304

Dimensions

Unit : mm

Part Number Steel	Part Number Stainless steel	M (coarse) 2	M ₁ (fine)	Lm	s	t	D	Mass (g)
SAD-M4-RF	SADS-M4-RF	M4	M4×0.5	4.5	1.4	0.6	7	0.9 - 2.5
SAD-M5-RF	SADS-M5-RF	M5	M5×0.5	4.5	1.6	0.6	9	1.5 - 6.3
SAD-M6-RF	SADS-M6-RF	M6	M6×0.75	5.5	2	0.6	9	2.2 - 11
SAD-M8-RF	SADS-M8-RF	M8	M8×1	6.5	2.5	0.8	12	3.9 - 26
SAD-M10-RF	SADS-M10-RF	M10	M10×1.25	8.5	3	0.8	16	8.2 - 41

SAD-RF Made of Steel SADS-RF Made of Stainless Steel

Part Number	L (mm) 3									
	12	16	20	25	32	40	50	63	80	
SAD-M4-RF	●	●	●	●	●					
SAD-M5-RF	●	●	●	●	●	●	●			
SAD-M6-RF	●	●	●	●	●	●	●	●		
SAD-M8-RF	●	●	●	●	●	●	●	●	●	
SAD-M10-RF		●	●	●	●	●	●	●	●	●
SADS-M4-RF	●	●	●	●	●					
SADS-M5-RF	●	●	●	●	●	●	●			
SADS-M6-RF	●	●	●	●	●	●	●	●		
SADS-M8-RF	●	●	●	●	●	●	●	●	●	●
SADS-M10-RF		●	●	●	●	●	●	●	●	●

● Related Products

Long-threaded type screw adaptor **SAD-FT** **SADS-FT** are available.

→ P.531



- Part number specification

SAD-M5-32-RF

1 **2** **3** Fine Screw Threaded Type

Cleanroom Wash & Packaging → P.792	Screw Combination → P.798	Screw Length Adjustment → P.796	Vibration Resistant → P.795
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge