


- 小径穴で安定した加工ができます。
- 生材から高硬度鋼の加工に最適です。

This drill is suitable for stable drilling in small diameter on most workpiece materials from raw material to hardened material.



LIST 9544

オーダ方法

AQMD 直径

切削条件 Drilling Condition ▶▶A-215

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
0.2	2.5	38	3	●	4,400
0.21	2.5	38	3	●	4,950
0.22	2.5	38	3	●	4,950
0.23	2.5	38	3	●	4,950
0.24	2.5	38	3	●	4,950
0.25	2.5	38	3	●	4,950
0.26	2.5	38	3	●	4,730
0.27	2.5	38	3	●	4,730
0.28	2.5	38	3	●	4,730
0.29	2.5	38	3	●	4,730
0.3	3	38	3	●	3,850
0.31	3	38	3	●	4,730
0.32	3	38	3	●	4,730
0.33	3	38	3	●	4,730
0.34	3	38	3	●	4,730
0.35	4	38	3	●	4,290
0.36	4	38	3	●	4,730
0.37	4	38	3	●	4,730
0.38	4	38	3	●	4,730
0.39	4	38	3	●	4,730
0.4	5	38	3	●	3,850
0.41	5	38	3	●	4,730
0.42	5	38	3	●	4,730
0.43	5	38	3	●	4,730
0.44	5	38	3	●	4,730
0.45	5	38	3	●	4,290
0.46	5	38	3	●	4,730
0.47	5	38	3	●	4,730
0.48	5	38	3	●	4,730
0.49	5	38	3	●	4,730
0.5	6	38	3	●	3,190
0.51	6	38	3	●	4,290
0.52	6	38	3	●	4,290
0.53	6	38	3	●	4,290
0.54	6	38	3	●	4,290
0.55	6	38	3	●	3,410
0.56	6	38	3	●	4,290
0.57	6	38	3	●	4,290
0.58	6	38	3	●	4,290
0.59	6	38	3	●	4,290
0.6	7	38	3	●	2,970
0.61	7	38	3	●	4,290
0.62	7	38	3	●	4,290
0.63	7	38	3	●	4,290
0.64	7	38	3	●	4,290
0.65	7	38	3	●	3,410
0.66	7	38	3	●	4,290
0.67	7	38	3	●	4,290
0.68	7	38	3	●	4,290
0.69	7	38	3	●	4,290
0.7	9	38	3	●	2,970
0.71	9	38	3	●	4,290
0.72	9	38	3	●	4,290
0.73	9	38	3	●	4,290
0.74	9	38	3	●	4,290
0.75	9	38	3	●	3,410
0.76	9	38	3	●	4,290
0.77	9	38	3	●	4,290
0.78	9	38	3	●	4,290
0.79	9	38	3	●	4,290

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
0.8	10	38	3	●	2,970
0.81	10	38	3	●	4,290
0.82	10	38	3	●	4,290
0.83	10	38	3	●	4,290
0.84	10	38	3	●	4,290
0.85	10	38	3	●	3,410
0.86	10	38	3	●	4,290
0.87	10	38	3	●	4,290
0.88	10	38	3	●	4,290
0.89	10	38	3	●	4,290
0.9	11	38	3	●	2,970
0.91	11	38	3	●	4,290
0.92	11	38	3	●	4,290
0.93	11	38	3	●	4,290
0.94	11	38	3	●	4,290
0.95	11	38	3	●	3,410
0.96	11	38	3	●	4,290
0.97	11	38	3	●	4,290
0.98	11	38	3	●	4,290
0.99	11	38	3	●	4,290
1	12	38	3	●	2,750
1.01	12	38	3	●	3,410
1.02	12	38	3	●	3,410
1.03	12	38	3	●	3,410
1.04	12	38	3	●	3,410
1.05	12	38	3	●	2,750
1.06	12	38	3	●	3,410
1.07	12	38	3	●	3,410
1.08	12	38	3	●	3,410
1.09	12	38	3	●	3,410
1.1	14	47	3	●	2,750
1.11	14	47	3	●	3,410
1.12	14	47	3	●	3,410
1.13	14	47	3	●	3,410
1.14	14	47	3	●	3,410
1.15	14	47	3	●	2,750
1.16	14	47	3	●	3,410
1.17	14	47	3	●	3,410
1.18	14	47	3	●	3,410
1.19	14	47	3	●	3,410
1.2	15	47	3	●	2,750
1.21	15	47	3	●	3,410
1.22	15	47	3	●	3,410
1.23	15	47	3	●	3,410
1.24	15	47	3	●	3,410
1.25	15	47	3	●	2,750
1.26	15	47	3	●	3,410
1.27	15	47	3	●	3,410
1.28	15	47	3	●	3,410
1.29	15	47	3	●	3,410
1.3	15	47	3	●	2,750
1.31	15	47	3	●	3,410
1.32	15	47	3	●	3,410
1.33	15	47	3	●	3,410
1.34	15	47	3	●	3,410
1.35	15	47	3	●	2,750
1.36	15	47	3	●	3,410
1.37	15	47	3	●	3,410
1.38	15	47	3	●	3,410
1.39	15	47	3	●	3,410