




MAGNETIC LIGHT STAND





FEATURES

- Auxiliary lighting improves visibility and quality
- Ferrite magnet
- Holding force : 800N (180 lb)
- Strong magnet with ON/OFF lever for easy removal
- Light is concentrated on workpiece
- Flexible stem directs light where needed
- Includes light guard
- Bulb : AC100V、100Watt or less
- ※ Bulb sold separately


Order No.	Model No.	Base Dimension (mm)	Height (mm)	Rated voltage	Rated Frequency	Weight
011090	MFR-100	50 × 60 × 55	440	AC100V	50-60Hz	1.7kg

FLEXIBLE LIGHT WITH MAGNET



FEATURES

- Locate and pick up small fasteners, temporary lighting for test, maintenance
- Flexible stem : Stainless steel
- With attached inspection mirror (φ38mm)
- LED for long usage life
- Adheres to steel surfaces for hands free operation
- Flexible stem conforms to any shape
- Magnet can also be used as pick-up tool
- Power : Three LR44 batteries included for testing



Order No.	Model No.	Continuous Lighting	Magnetic Force	Weight
011092	MFL-350M	Approx. 12 hrs	Tip 0.5N Bottom 10N	150g