


●鋼からステンレス鋼まで、汎用コバルトドリルです。

This is general cobalt HSS drills.



切削条件 Drilling Condition : A-237

単位 (Unit) : mm / 円 (¥)

LIST 6520

オーダー方法

COSD 直径

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
0.5	5	27	●	568
0.6	5.5	30	●	571
0.7	7.5	32	●	531
0.8	8	34	●	447
0.9	9	36	●	481
1.0	10	40	●	406
1.1	11	42	●	476
1.2	13	42	●	446
1.3	13	45	●	476
1.4	14.5	48	●	476
1.5	14.5	48	●	403
1.6	16	50	●	438
1.7	16	50	●	476
1.8	17.5	52	●	454
1.9	17.5	52	●	454
2.0	20	55	●	396
2.1	20	55	●	465
2.2	23	58	●	465
2.3	23	58	●	440
2.4	24.5	61	●	465
2.5	24.5	61	●	396
2.6	26	64	●	440
2.7	26	64	●	440
2.8	27	67	●	433
2.9	29.5	71	●	440
3.0	29.5	71	●	368
3.1	29.5	71	●	516
3.2	29.5	71	●	450
3.3	31.5	73	●	450
3.4	31.5	73	●	497
3.5	31.5	73	●	450
3.6	33.5	76	●	549
3.7	33.5	76	●	549
3.8	33.5	76	●	500
3.9	36	79	●	575
4.0	38	83	●	500
4.1	38	83	●	659
4.2	38	83	●	599
4.3	38	83	●	659
4.4	39	86	●	659
4.5	39	86	●	599
4.6	39	86	●	755
4.7	41	89	●	755
4.8	41	89	●	755
4.9	43	92	●	794
5.0	43	92	●	688
5.1	43	92	●	879
5.2	45	95	●	801
5.3	45	95	●	879
5.4	45	95	●	879
5.5	45	95	●	801
5.6	47	98	●	1,020
5.7	47	98	●	1,020
5.8	47	98	●	1,020
5.9	47	98	●	1,060
6.0	49	102	●	921
6.1	49	102	●	1,160
6.2	49	102	●	1,160
6.3	49	102	●	1,160
6.4	51	105	●	1,160

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格 Price
6.5	51	105	●	1,040
6.6	51	105	●	1,300
6.7	51	105	●	1,300
6.8	51	105	●	1,300
6.9	51	105	●	1,400
7.0	51	105	●	1,180
7.1	53	108	●	1,590
7.2	53	108	●	1,520
7.3	53	108	●	1,590
7.4	55	111	●	1,590
7.5	55	111	●	1,410
7.6	55	111	●	1,800
7.7	57	114	●	1,730
7.8	57	114	●	1,700
7.9	57	114	●	1,800
8.0	57	114	●	1,480
8.1	59	117	●	1,950
8.2	59	117	●	1,910
8.3	59	117	●	1,950
8.4	61	121	●	2,010
8.5	61	121	●	1,800
8.6	61	121	●	2,190
8.7	61	121	●	2,190
8.8	63	124	●	2,260
8.9	63	124	●	2,260
9.0	63	124	●	1,870
9.1	63	124	●	2,470
9.2	65	127	●	2,560
9.3	65	127	●	2,500
9.4	65	127	●	2,560
9.5	65	127	●	2,270
9.6	67	130	●	2,720
9.7	67	130	●	2,720
9.8	67	130	●	2,720
9.9	67	130	●	2,960
10.0	67	130	●	2,370
10.1	69	133	●	3,360
10.2	69	133	●	3,160
10.3	69	133	●	3,160
10.4	69	133	●	3,360
10.5	70	137	●	2,860
10.6	70	137	●	3,960
10.7	70	137	●	3,960
10.8	72	140	●	3,960
10.9	72	140	●	3,960
11.0	72	140	●	3,010
11.1	72	140	●	4,170
11.2	75	143	●	4,010
11.3	75	143	●	4,170
11.4	75	143	●	4,010
11.5	75	143	●	3,510
11.6	77	146	●	4,330
11.7	77	146	●	4,530
11.8	77	146	●	4,330
11.9	77	146	●	4,530
12.0	78	149	●	3,540
12.1	78	149	●	4,720
12.2	78	149	●	4,720
12.3	78	149	●	4,720
12.4	80	152	●	4,950

総目次

Non Coat

穴深さ

~3D

~5D

~7D

~9D

深穴

ノスドリル

鉄骨

油穴付き

アルミ・非鉄金属

ストレート

テーパ