

THICKNESS GAUGE WITH COLOR SLEEVE



Same accuracy as regular THICKNESS GAUGE with three different color options - white, black and green



USE

- For measurement of gap width

MATERIAL

- Carbon tool steel

FEATURES

- Enables precise inspection by inserting the gauge into the gap between two flat surfaces
- Suitable for measuring gap between piston and cylinder of automotive engine
- Each of the gauges can be detached by unscrewing the clip of the cover (except 172 series)
- Leaf Width: 12.7mm
- ※ Please specify color (White, Black, Green) at the time of order placement
- ※ White powder remains on the surface of the product is antirust agent

For cutting necessary size▶ Feeler Gauge P86 ~87	Replaceable leaf▶ Thickness Gauge Leaf P89
Rust-resistant type▶ Stainless Thickness Gauge P90	Rust prevention▶ Zerust Film for Steel P380

ACCURACY

Leaf thickness (mm)	Tolerance (mm)
0.01~0.06	±0.005
0.07~0.10	±0.01
0.11~0.35	±0.015
0.40~0.60	±0.02
0.70~3.00	±0.035

Model No.	Leaf Length (mm)	Pieces/ Set	Size (mm)	Weight
CS-172MA	75	9	0.04 0.05 0.06 0.07 0.08 0.10 0.15 0.20 0.30	30g
CS-172MB	100		30g	
CS-172MC	150	10	0.03 0.04 0.05 0.08 0.10 0.15 0.20 0.25 0.30 0.40	50g
CS-100MR	100		40g	
CS-150MR	150		60g	
CS-100MK	100	10	0.01 0.02 0.03 0.04 0.05 0.06 0.07 0.08 0.09 0.10	30g
CS-150MK	150		40g	
CS-60M	75	19	0.03 0.04 0.05 0.06 0.07 0.08 0.09 0.10 0.15 0.20	60g
CS-100MY	100		80g	
CS-150MY	150		120g	
CS-65M	75	25	0.03 0.04 0.05 0.06 0.07 0.08 0.09 0.10 0.11 0.12	80g
CS-100MZ	100		100g	
CS-150MZ	150		150g	
CS-72M	75	12	0.04 0.05 0.06 0.07 0.08 0.10 0.15 0.20 0.30 1.00	70g
CS-100MT	100		100g	
CS-150MT	150	19	2.00 3.00	140g
CS-100ML	100		80g	
CS-150ML	150		120g	
CS-80M	75	13	0.01 0.02 0.03 0.04 0.05 0.06 0.07 0.08 0.09 0.10	60g
CS-100MX	100		90g	
CS-150MX	150		140g	
CS-100MH	100	10	1.00 2.00 3.00	80g
CS-150MH	150		110g	

THICKNESS GAUGE LEAF



MATERIAL

- Carbon tool steel
- Leaf Width: 12.7mm
- ※ White powder remains on the surface of the product is antirust agent

For cutting necessary size▶ Feeler Gauge P86 ~87	Rust prevention▶ Zerust Film for Steel P380
--	---

■ Leaf Length: 100mm

Order No.	Model No.	Thickness (mm)
110801	S100-001	0.01
110802	S100-002	0.02
110803	S100-003	0.03
110804	S100-004	0.04
110805	S100-005	0.05
110806	S100-006	0.06
110807	S100-007	0.07
110808	S100-008	0.08
110809	S100-009	0.09
110810	S100-01	0.10
110811	S100-02	0.20
110812	S100-03	0.30
110813	S100-04	0.40
110814	S100-05	0.50
110815	S100-06	0.60
110816	S100-07	0.70
110817	S100-08	0.80
110818	S100-09	0.90
110819	S100-10	1.00

■ Leaf Length: 150mm

Order No.	Model No.	Thickness (mm)
110820	S150-001	0.01
110821	S150-002	0.02
110822	S150-003	0.03
110823	S150-004	0.04
110824	S150-005	0.05
110825	S150-006	0.06
110826	S150-007	0.07
110827	S150-008	0.08
110828	S150-009	0.09
110829	S150-01	0.10
110830	S150-02	0.20
110831	S150-03	0.30
110832	S150-04	0.40
110833	S150-05	0.50
110834	S150-06	0.60
110835	S150-07	0.70
110836	S150-08	0.80
110837	S150-09	0.90
110838	S150-10	1.00